







FCIconnect.com

Copyright FCI

view shown without plastic pin and grounding




Detail of grounding strip



PC card drilling dimensions(after plating)

(thickness 1.60 ±0.20)



TIN LEAD PART NUMBER

SHELL	A± 0.38	B± 0.12	C± 0.10	D+0.25 0	E± 0.07	G	PART NUMBER	PART NUMBER
09	30.81	24.99	18.00	16.79	10.96	5.90+0.15 0	D09P81C4PV00	D09P81C6PV00
15	39.14	33.32	26.32	25.12	19.18	5.90+0.15 0	D15P81C4PV00	D15P81C6PV00
25	53.03	47.04	40.04	38.84	33.12	5.70+0.25 0	D25P81C4PV00	D25P81C6PV00
37	69.32	63.50	56.50	55.30	49.68	5.70+0.25 0	D37P81C4PV00	D37P81C6PV00
Gold flash							0.76 µ gold	

LEAD FREE PART NUMBER

SHELL	A± 0.38	B± 0.12	C± 0.10	D+0.25 0	E± 0.07	G	PART NUMBER	PART NUMBER
09	30.81	24.99	18.00	16.79	10.96	5.90+0.15 0	D09P81C4PV00LF	D09P81C6PV00LF
15	39.14	33.32	26.32	25.12	19.18	5.90+0.15 0	D15P81C4PV00LF	D15P81C6PV00LF
25	53.03	47.04	40.04	38.84	33.12	5.70+0.25 0	D25P81C4PV00LF	D25P81C6PV00LF
37	69.32	63.50	56.50	55.30	49.68	5.70+0.25 0	D37P81C4PV00LF	D37P81C6PV00LF
Gold flash							0.76 µ gold	

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0001

mat'l. code				surface	tolerance	projection	product family		
-				ISO 1302	ISO 406 ISO 1101		D-SUB		
ltr	ecn no	dr	date	tolerances unless otherwise specified			title		
D	ELX-I-18050	MP	2014/06/23	angles	linear		MALE CONNECTOR DELTA-D EUROPE		
				0°±2°			RIGHT ANGLED PRESS FIT		
				dr	JOUBERT	1997/10/20	dwg no		sheet 1 of 1
				engr	MITHUN PAUL	2014/06/23	C01-8646-0584		A3
				chr	ALIAS BABU	2014/06/23	type Product Customer Drawing		
				appd	BIJU K PAUL	2014/06/23			
sheet index	revision sheet	D	1						