

# Product Information

## 3477UVH080P62

EAN 4031582306217

Swivel castor with total lock, tail end of caster,  
Housing made of pressed steel, zinc-chromatised,  
double ball bearing swivel head, wheel axle with nut,  
dustguard.

Wheel centre made of Polyamide, Tread: solid  
rubber, black, plain bearing, with threadguards,, plate  
fitting

Wheel diameter	80 mm
Width of Tread	35 mm
Size of Plate	105 x 85 mm
Plate hole centres	80/77 x 60 mm
Plate hole	9 mm
Offset	44.5 mm
Swivel Interference	246 mm
Overall height	108 mm
Temperature	- 20 / + 60 °C
Standard	EN 12532
Weight	0.95 Kg / daN
Dynamic Load capacity	100 Kg / daN
Static Load capacity	200 Kg / daN
Hardness of tread	A 95 Shore



### Versions:

