

JOURNEYMAN

Series

The Journeyman™ line of hand tools represents the best of Klein quality and workmanship combined with the latest innovations in handle design.



For Professionals...
Since 1857™



State-of-the-art dual material molding process

Induction hardened cutting knives for long life

Hot-riveted joint ensures smooth action and no handle wobble

Contoured thumb area for additional comfort and positive feel

Hard, black material for toughness and durability

MADE IN USA

2000 Series™
HEAVY-DUTY CUTTING

pliers available.

Cuts ACSR, screws, nails, and most hardened wire

Soft material on outer surface for comfort and a firm grip

US Patent: D468988

Side-Cutting Pliers

High-Leverage Side-Cutting Pliers

Additional Features:

- High-leverage design. Rivet is closer to the cutting edge for 46% greater cutting and gripping power than other pliers designs
- Streamlined design with sure-gripping, cross-hatched knurled jaws



J2000-9NE

Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Handle Finish	Handle Color	Weight
J2138NE	New England	8-13/16" (223.8 mm)	1-7/16" (36.5 mm)	1-3/16" (30.2 mm)	5/8" (15.9 mm)	23/32" (18.3 mm)	Journeyman	Dark Blue/Black	15.5 oz. (439 g)
J213-9NE	New England	9-1/2" (241.3 mm)	1-19/32" (40.5 mm)	1-1/4" (31.8 mm)	5/8" (15.9 mm)	25/32" (19.8 mm)	Journeyman	Dark Blue/Black	1.1 lbs. (0.50 kg)
2000 Series* – Heavy-duty cutting knives									
J20008	New England Tapered	8-13/16" (223.8 mm)	1-7/16" (36.5 mm)	1-7/64" (28.2 mm)	5/8" (15.9 mm)	3/4" (19.1 mm)	Journeyman	Light Blue/Black	14.9 oz. (422 g)
J2000-9NE	New England	9-1/2" (241.3 mm)	1-19/32" (40.5 mm)	1-1/4" (31.8 mm)	5/8" (15.9 mm)	25/32" (19.8 mm)	Journeyman	Light Blue/Black	1.1 lbs. (0.50 kg)

*Cuts ACSR, screws, nails, and most hardened wire. Features combination polished and black-oxide finish.

High-Leverage Side-Cutting Pliers - Fish-Tape Pulling

Additional Features:

- Easily pulls 1/8" or 1/4" flat steel fish tape without damaging the tape
- High-leverage design. Rivet is closer to the cutting edge for 46% greater cutting and gripping power than other pliers designs
- Streamlined design with sure-gripping, cross-hatched knurled jaws



J2000-9NETP

Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Handle Finish	Handle Color	Weight
J213-9NETP	New England	9-1/2" (241.3 mm)	1-19/32" (40.5 mm)	1-1/4" (31.8 mm)	5/8" (15.9 mm)	25/32" (19.8 mm)	Journeyman	Dark Blue/Black	1.1 lbs. (0.50 kg)
2000 Series* – Heavy-duty cutting knives									
J2000-9NETP	New England	9-1/2" (241.3 mm)	1-19/32" (40.5 mm)	1-1/4" (31.8 mm)	5/8" (15.9 mm)	25/32" (19.8 mm)	Journeyman	Light Blue/Black	1.1 lbs. (0.50 kg)

*Cuts ACSR, screws, nails, and most hardened wire. Features combination polished and black-oxide finish.

High-Leverage Side-Cutting Pliers - Connector Crimping

Additional Features:

- Crimping die behind hinge for superior leverage crimping noninsulated connectors, lugs and terminals
- High-leverage design. Rivet is closer to the cutting edge for 46% greater cutting and gripping power than other pliers designs
- Streamlined design with sure-gripping, cross-hatched knurled jaws



J213-9NECR

Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Handle Finish	Handle Color	Weight
J213-9NECR	New England	9-1/2" (241.3 mm)	1-19/32" (40.5 mm)	1-1/4" (31.8 mm)	5/8" (15.9 mm)	25/32" (19.8 mm)	Journeyman	Yellow/Black	1.1 lbs. (0.50 kg)
2000 Series* – Heavy-duty cutting knives									
J2000-9NECR	New England	9-1/2" (241.3 mm)	1-19/32" (40.5 mm)	1-1/4" (31.8 mm)	5/8" (15.9 mm)	25/32" (19.8 mm)	Journeyman	Light Blue/Black	1.1 lbs. (0.50 kg)

*Cuts ACSR, screws, nails, and most hardened wire. Features combination polished and black-oxide finish.



Side-Cutting Pliers

High-Leverage Side-Cutting Pliers - Connector Crimping & Stripping

Additional Features:

- Built-in crimper works on non-insulated connectors, lugs, and terminals
- Cleanly strips 10 and 12 solid AWG wire and 12 and 14 stranded wire
- High-leverage design. Rivet is closer to the cutting edge for 46% greater cutting and gripping power than other pliers designs
- Streamlined design with sure-gripping, cross-hatched knurled jaws



J2139NECRN

Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Handle Finish	Handle Color	Weight
J2139NECRN	New England	9-1/2" (241.3 mm)	1-19/32" (40.5 mm)	1-1/4" (31.8 mm)	5/8" (15.9 mm)	25/32" (19.8 mm)	Journeyman	Yellow/Black	1.1 lbs. (0.50 kg)

High-Leverage Side-Cutting Pliers - Connector Crimping & Fish Tape Pulling

2000TM series

Additional Features:

- Built-in crimper works on non-insulated connectors, lugs, and terminals
- Built-in channel pulls steel fish tape without damaging the tape
- High-leverage design. Rivet is closer to the cutting edge for 46% greater cutting and gripping power than other pliers designs
- 2000 series heavy-duty cutting knives cut ACSR, screws, nails, and most hardened wire
- Combination polished and black-oxide finishes



J2000-9NECRTP

Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Handle Finish	Handle Color	Weight
J2000-9NECRTP	New England	9-1/2" (241.3 mm)	1-19/32" (40.5 mm)	1-1/4" (31.8 mm)	5/8" (15.9 mm)	25/32" (19.8 mm)	Journeyman	Blue/Black	1.1 lbs. (0.50 kg)

High-Leverage Universal Combination Pliers

Additional Features:

- Universal tapered head-design allows greater access in confined spaces
- Precision machined pipe-grip for greater gripping power
- Crimping die behind hinge for superior leverage crimping of non-insulated connectors, lugs and terminals



J12098

Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Handle Finish	Handle Color	Weight
J12098	Universal	8-3/4" (222.3 mm)	1-25/32" (45.2 mm)	1-1/32" (26.2 mm)	17/32" (13.5 mm)	3/4" (19.1 mm)	Journeyman	Dark Blue/Black	13.1 oz. (371 g)

Side-Cutting Pliers

2000TM series

Additional Features:

- 2000 series heavy-duty cutting knives cut ACSR, screws, nails, and most hardened wire
- Combination polished and black-oxide finishes



J2001-7NE

Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Handle Finish	Handle Color	Weight
J20017NE	New England	7-9/16" (192.1 mm)	1-9/32" (32.5 mm)	1-1/16" (27.0 mm)	1/2" (12.7 mm)	5/8" (15.9 mm)	Journeyman	Light Blue/Black	9.8 oz. (278 g)



Diagonal-Cutting Pliers

High-Leverage Diagonal-Cutting Pliers

Additional Features:

- High-leverage design. Rivet is closer to the cutting edge for 36% greater cutting and gripping power than other plier designs
- Short jaws and beveled cutting edges permit close cutting of wire
- Cat. Nos. J248-8 and J2000-48 have an angled head design for easy work in confined spaces



J2000-28



Angled Head Profile

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Cutting Knives	Handle Finish	Handle Color	Weight
J228-8	8-1/8" (206.4 mm)	13/16" (20.6 mm)	1-3/16" (30.2 mm)	7/16" (11.1 mm)	Standard	Journeyman	Red/Black	10.7 oz. (303 g)
J248-8	8-1/8" (206.4 mm)	13/16" (20.6 mm)	1-3/16" (30.2 mm)	7/16" (11.1 mm)	Standard	Journeyman	Red/Black	9.8 oz. (278 g)
2000 Series* – Heavy-duty cutting knives								
J2000-28	8-1/8" (206.4 mm)	13/16" (20.6 mm)	1-3/16" (30.2 mm)	7/16" (11.1 mm)	Standard	Journeyman	Light Blue/Black	10.7 oz. (303 g)
J2000-48	8-1/8" (206.4 mm)	13/16" (20.6 mm)	1-3/16" (30.2 mm)	7/16" (11.1 mm)	Standard	Journeyman	Light Blue/Black	9.8 oz. (278 g)

Long-Nose Pliers

All-Purpose Pliers

Additional Features:

- Cat. No. J206-8C strips 8-16 AWG solid and 10-18 AWG stranded wire
- Cat. No. J207-8CR strips 10-18 AWG solid and 12-20 AWG stranded wire and crimps non-insulated connectors, lugs and terminals
- Long nose for grabbing and looping wire
- 6-32 and 8-32 screw shearing



J206-8C



J207-8CR

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Point Thickness	Handle Finish	Handle Color	Weight
J206-8C	8-5/8" (219.1 mm)	2-3/16" (55.6 mm)	1" (25.4 mm)	1/2" (12.7 mm)	1/2" (12.7 mm)	1/8" (3.2 mm)	Journeyman	Yellow/Black	9.6 oz. (272 g)
J207-8CR	8-5/8" (219.1 mm)	2-3/16" (55.6 mm)	1" (25.4 mm)	1/2" (12.7 mm)	1/2" (12.7 mm)	1/8" (3.2 mm)	Journeyman	Yellow/Black	9.6 oz. (272 g)

Heavy-Duty Long-Nose Pliers - Side-Cutting

Additional Features:

- Heavier design for greater cutting power
- Slim head design for working in confined areas



J203-8

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Point Thickness	Handle Finish	Handle Color	Weight
J203-8	8-9/16" (217.5 mm)	2-5/16" (58.7 mm)	1" (25.4 mm)	1/2" (12.7 mm)	5/8" (15.9 mm)	1/8" (3.2 mm)	Journeyman	Yellow/Black	10.1 oz. (286 g)
Wire Stripping – Cleanly strips 12 AWG wire									
J203-8N	8-9/16" (217.5 mm)	2-5/16" (58.7 mm)	1" (25.4 mm)	1/2" (12.7 mm)	5/8" (15.9 mm)	1/8" (3.2 mm)	Journeyman	Yellow/Black	10.2 oz. (289 g)



Long-Nose Pliers

Standard Long-Nose Pliers - Side-Cutting

Additional Features:

- Slim head design for working in confined areas
- Knurled jaws for sure wrapping and looping



J203-7

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Point Thickness	Handle Finish	Handle Color	Weight
J203-7	7-5/16 (185.7 mm)	2-7/16" (61.9 mm)	11/16" (17.5 mm)	3/8" (9.5 mm)	1/2" (12.7 mm)	3/32" (2.4 mm)	Journeyman	Yellow/Black	5.3 oz. (150 g)
J203-6	6-3/4" (171.5 mm)	1-7/8" (47.6 mm)	11/16" (17.5 mm)	3/8" (9.5 mm)	1/2" (12.7 mm)	3/32" (2.4 mm)	Journeyman	Yellow/Black	4.8 oz. (136 g)

Pump Pliers

Pump Pliers

Additional Features:

- Secure tongue and groove design for non-slip grip - even with heavy pressure
- Wide range of versatile jaw positions
- Tension-loaded joint to reduce handle wobble for sure gripping



J502-10

Cat. No.	Overall Length	Max. Jaw Capacity	Handle Finish	Handle Color	Weight
J502-10	10-1/4" (260.4 mm)	1-3/4" (44.5 mm)	Journeyman	Yellow/Black	1.0 lbs. (0.45 kg)

Crimping/Cable Cutting Tools

Crimping/Cutting Tool - Non-Insulated/Insulated Connectors

Additional Features:

- Designed to crimp insulated and non-insulated 10 to 22 AWG solderless terminals and connectors
- Tapered nose design for working in confined spaces
- Contoured thumb area for additional comfort and positive feel
- Specially hardened cutter



J1005

Cat. No.	Overall Length	Handle Finish	Handle Color	Crimps	Weight
J1005	9-3/4" (247.7 mm)	Journeyman	Red/Black	10 - 22 AWG (4.0 mm ² - 0.34 mm ²)	13.4 oz. (381 g)

High-Leverage Cable Cutter

Additional Features:

- Cuts up to 4/0 aluminum AWG (no ACSR), 2/0 AWG soft copper and 100-pair 24 AWG communications cable
- High-leverage for greater cutting power
- Precision, one-hand shearing action
- Do NOT use to cut steel or ACSR



J63050

Cat. No.	Overall Length	Maximum Cable Cutting Capacity	Handle Finish	Handle Color	Weight
J63050	9-9/16" (242.9 mm)	4/0 Aluminum, 2/0 Soft Copper, 100-Pair 24 AWG Communications Cable	Journeyman	Red/Black	15.7 oz. (445 g)