



2410 StealthLite™

Same features as the StealthLite™ 2400 Flashlight, but with the LED module that produces a true, bright collimated LED beam. The 2410 is corrosion proof, resistant to extreme temperatures, and submersible. It is powered by 4 AA alkaline cells (included). For hands-free operation, attach it to your hard hat with our optional helmet light holder.

- As bright as a Xenon light with the battery life of an LED
- Built Pelican tough
- Super bright LED beam
- Unconditional Lifetime Guarantee of Excellence
- **NOW WITH NEW UPGRADED SPECS**
- Waterproof



DIMENSIONS

Length	7.00" (17.8 cm)
---------------	-----------------

MATERIALS

Body	EXL
O-Ring	Ethylene Propylene
Lens	Polycarbonate (PC)
Shroud	ABS
Contact Spring Retainer	Stainless Steel / Phosphore Bronze

COLORS

 Black	 High Visibility Yellow
---	--

LIGHT SPECS

Lamp Type	LED
------------------	-----

POWER

Battery Size	AA
Battery Type	Alkaline
Battery Quantity	4
Batteries Included	yes
Volts	6.0v

WEIGHT

Weight With Batteries	7.3 oz (207 gr)
Weight Without Batteries	3.7 oz (105 gr)
Packaged Weight	8.4 oz (238 gr)

SWITCH

23215 Early Ave • Torrance, CA 90505 USA • Phone: (310) 326-4700 • (800) 473-5422 • Fax: (310) 326-3311

Pelican

Switch Type

One-handed Safety Switch

Light Modes

On / Off

sales@pelican.com • www.pelican.com

Document created on 08-15-20

CERTIFICATIONS

Class I, Division 1

Class II, Division 1

Class III, Division 1

IECEX ia

OTHER

Submersible

yes

Minimum Pack






6

Military

yes

Package Code

C

FL1 STANDARD	HIGH
	183 LUMENS
	5h 45mins
	184m
	8480cd
	IPX7

ACCESSORIES