


Dimensions: mm (In.)



POS.1	POS.2	POS.3
ON	NONE	ON
2-3		2-1
	OPEN	

SWITCH FUNCTION

Electrical Specifications:

- Electrical Life: 40,000 make-and-break cycles at full load
- Contact Resistance: 10mΩ max. initial @ 2-4VDC 100mA
- Insulation Resistance: 1,000MΩ min.
- Rating: 2A / 250 VAC, 5A / 120 VAC or 28 VDC
- Dielectric Strength: 1,000 V RMS@ sea level.

Mechanical Specifications:

- Operating Temperature: -30° C to +85° C

Materials:

- Case: Dialyl phthalate (DAP)
- Actuator: Brass, chrome plated
- Bushing: Brass, nickel plated
- Housing: Stainless steel
- Terminal/Contact: Silver or Gold plated

Toggle Switch
108-1MS1T1B1M2QE

Mountain
Switch

Available from Mouser Electronics

www.mouser.com 1-800-346-6873

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[108-1MS1T1B1M2QE](#)