

INTRINSICALLY SAFE

- Approved by global agencies for intrinsically safe lights



IDENTIFIABLE

- Internationally approved orange safety color



WATERPROOF

- Protects interior components from water damage
- IP67



IMPACT RESISTANT

- Survives a 2 meter drop



ECONOMICAL

- Reduced battery consumption for cost savings
- 17 hour run time



MS2ALED

European Region

Approved by global safety agencies, the MS2ALED is ideal for work in harsh conditions. The light is waterproof, dustproof and survives a 2 meter drop test.

A built-in carabiner belt clip allows quick access and the compact size fits easily in any toolbox. Internationally approved, the safety orange color provides instant recognition. The White LED lamp supplies steady, bright illumination.



APPROVED BY:

- UL913 Class I, II and III
- CAN/CSA C22.2 No. 157-92
- IEC 60529 – IP67
- ATEX
- IECEX
- CE 0539 IM2/II1G EEx ia/IIC T4
- DEMKO 07 ATEX 0618226

Before Using Your Flashlight:


Please read all instructions and cautionary markings on the package and light

European Region

Product Detail:

Designation:	Energizer 2AA ATEX
Model:	MS2ALED
Color:	Safety Orange and Black
Power Source:	Two "AA"
ANSI/NEDA:	15 Series
Lamp:	Three White Nichia GS LEDs
Lamp Output Rating:	30 Lumens
Runtime:	17 Hours
Durability:	Survives 2 meter drop
Typical Weight:	66 grams (without batteries)
Dimensions (mm):	151.6 x 35.1 x 40.6

Performance:



Important Notice

This datasheet contains information specific to products manufactured at the time of its publication

Contents herein do not constitute a warranty
©Energizer / All Rights Reserved