

LOGO! TD TEXTDISPLAY,
FOR LOGO! FROM ..0BA6, 4 LINES,
WITH CABLE (2.5M) AND MOUNTING ACCESSORIES,
CONFIGURATION WITH LOGO! SOFT COMFORT V6.0



General information	
Application area	Connection to all LOGO! basic units from ..0BA6
Delivery quantity in pieces	1
Operator control and monitoring	
Illuminant	LED
Operating / fault messages	
Number of lines	4
Number of characters per line	24
Display	
Design of display	STN
graphics-enabled	No
Control elements	
Keyboard fonts	
Keys with LED	No
Number of configurable system keys	15
System keys	Yes
Numeric/alphabetical input	
Numeric keyboard	No
Alphanumeric keyboard	No

Supply voltage	
Type of supply voltage	DC
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Interfaces	
Number of RS 232 interfaces	1
Number of other interfaces	1
Industrial Ethernet	
Number of industrial Ethernet interfaces	0
Degree and class of protection	
IP40	Yes
Ambient conditions	
Operating temperature	
Min.	0 °C
max.	55 °C
Accessories	
Function description	Connecting cable length 2.5 m
belongs to product	LOGO!
Dimensions	
Width	128.2 mm
Height	86 mm
Depth	38.7 mm
Dimensions and weight	Length 2.5 m
Weight	
Weight, approx.	220 g
Status	Apr 20, 2013