



Sample photo

Order symbol: PCM 125/60 G
Product nbr: 6016307
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074038036
El. number:
Finland: 3421635
Electric No. Denmark: 8212027064
Electric No. Italy: 7341025
Electric No. Sweden: 2535312

Including: Base with metric knock-outs and TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:	Length	Width	Height
mm:	130	130	60
inch:	5.1	5.1	2.4

Materials:

Material: Polycarbonate
Base colour: RAL 7035 -light grey
Cover screws material: Polyamide
Cover colour: RAL 7035 -light grey
Cover screws colour: Grey
Gasket material: TPE

Temperatures:

Temperature °C (short term): -40 ... 120 °C
Temperature °C (continuous): -40 ... 80 °C
Temperature °F (short term): -40 ... 250 °F
Temperature °F (continuous): -40 ... 175 °F

Accessories:

MIV 125 Mounting plate (Galvanized steel)

Accessories:

MIN 10 DIN-15 Mounting rail
MIV 10 DIN-35 Mounting rail
FP A 125/130 Front plate (Aluminium)
HFP 130 Front plate hinge series
FP 22046 Wall fastening lug (4 pcs)

Rating:

Ingress Protection (EN 60529): IP66/67
Impact Resistance (EN 62262): IK08
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): 1
UV resistance: UL 508
Flammability Rating: UL 746C 5V
Glow Wire Test (IEC 695-2-1) °C: 960
NEMA Class: NEMA 1, 4, 4X, 6

Certificates:

Germanischer Lloyd (GL)
SGS Fimko
Gost R

