



Sample photo

Order symbol: EKMB 130 G
Product nbr: 2538019
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074013507
El. number:
Finland: 3425409
Italy: 7501025
Sweden: 2538019
Norway:

Including: Flanged Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		380	190	130	Ingress Protection (EN 60529): IP 66/67
inch:		15.0	7.5	5.1	Impact Resistance (EN 62262): IK 08
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			UV resistance: UL 508
Cover colour:		RAL 7035			Flammability Rating (UL 746 C 5): UL 746C 5V
Cover screws material:		Polyamide			Glow Wire Test (IEC 695-2-1) °C: 960
Cover screws colour:		Grey			NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12
Gasket material:		Polyurethane			
Temperatures:					Certificates:
Short term:		-40 ... 120 °C			Germanischer Lloyd (GL)
Continuous:		-40 ... 80 °C			Underwriters Laboratories
Short term:		-40 ... 250 °F			Det Norske Veritas
Continuous:		-40 ... 175 °F			Bureau Veritas
Accessories:					Fimko
EKMB		Base, PC			Lloyds Register of Shipping (LR)
EKMR		Base, PC			Europe EN 62208: 2003
EKM 30-G		Cover			UL Canada
EKM 80-G		Cover			Gost R
EKM 30-T		Cover			
EKM 80-T		Cover			
EKMVT		Mounting plate			
EKMXT		Mounting plate Pertinax			
EKV 12		DIN-35 Mounting rail			
EKV 32		DIN-35 Mounting rail			
EKMZR		Extension frame			

EK 380x190x130-180

