





Front panels

as filler panel, flat

Material:

2.5 mm aluminium, natural anodised.



Also required:

Captive screws and plastic collars, packs of 100 set, Model No. RP 3658.160, see page 576.

HP	a mm	B mm	b mm	Model No. RP						
				1 U H = 39.8	2 U H = 84.25	3 U H = 128.7	4 U H = 173.15	6 U H = 262.05	7 U H = 306.5	9 U H = 395.4
2	9.8	–	–	–	–	3684.889	–	3684.911	–	3684.738
3	14.9	–	–	–	–	3684.890	–	3684.912	–	–
4	20.0	–	–	–	–	3684.891	–	3684.913	–	3684.739
5	25.1	–	–	–	–	3684.892	–	3684.914	–	–
6	30.1	–	–	–	–	3684.893	–	3684.915	–	–
7	35.2	–	–	–	–	3684.894	–	3684.916	–	–
8	40.3	–	–	–	–	3684.895	–	3684.917	–	3684.740
10	50.5	35.6	–	–	–	3684.896	–	3684.918	–	–
12	60.6	45.7	–	–	–	3684.897	–	3684.919	–	3684.741
14	70.8	55.9	–	–	–	3684.898	–	3684.920	–	–
20	101.3	86.4	–	–	–	3684.899	–	3684.921	–	–
21	106.4	91.4	–	–	3685.350	3684.900	–	3684.922	–	–
24	121.7	106.7	–	–	3685.429	–	–	–	–	–
27	136.8	121.9	–	–	–	3684.901	–	3684.923	–	–
28	141.9	127.0	–	–	–	3684.902	–	3684.924	–	–
40	202.9	188.0	–	–	–	3684.903	–	3684.976	–	3684.977
42	213.0	198.1	–	3684.885	3684.887	3684.904	3684.908	3684.925	3684.928	3684.742
60	304.5	289.6	–	–	–	3684.905	–	–	–	–
63	319.7	304.8	152.4	–	–	3684.906	3684.909	3684.926	3684.929	–
84	426.4	411.5	203.2	3684.886	3684.888	3684.907	3684.910	3684.927	3684.930	3684.743
85	413.5	411.5	203.2	–	–	3684.744	3684.745	3684.746	3684.747	3684.748