

HC-49/U




Features and Applications:

- General, industrial, microcontrollers
- Cost Effective
- Well established product
- Wide frequency range
- Superior resistance weld HC-49/U metal case



Supplied loose as standard. Taped product available to special order



Dimensions : Millimetres

Specification Table

Nominal Frequency Range	1.8 to 32 MHz	24 to 75 MHz	75 to 200 MHz
Vibration Mode	Fundamental (AT)	3rd Overtone (AT)	5th Overtone (AT)
Frequency Tolerance at 25°C	±20 or ± 30 ppm		
Temperature Stability	±30 or ± 50 ppm		
Operating Temperature Range	-10°C to +60°C (Option : -20°C to +70°C)		
Storage Temperature Range	-20°C to +70°C (Option : -30°C to +80°C)		
Load Capacitance	8 pF to 32 pF or series		
Equivalent Series Resistance	See ESR table below		
Shunt Capacitance	5 pF maximum (≤18 MHz) or 7 pF maximum (>18 MHz)		
Drive Level	200 µW maximum (≤5 MHz) 100 µW maximum (>5 MHz)		
Insulation Resistance	500 MΩ minimum at 100 V dc		
Aging	±5 ppm per year		

ESR Table

Case	Vibration	HC 49U
Frequency	Mode	Ω Maximum
1 - 1,8 MHz	F	3,000
1.8 - 2 MHz	F	500
2.01 - 2.399 MHz	F	450
2.4 - 2.99 MHz	F	300
3 - 3.5 MHz	F	150

ESR Table

Case	Vibration	HC 49U
Frequency	Mode	Ω Maximum
3.5 - 3.99 MHz	F	90
4 - 4.99 MHz	F	80
5 - 5.99 MHz	F	70
6 - 6.99 MHz	F	60
7 - 7.99 MHz	F	50
8 - 9.99 MHz	F	40
10 - 13.99 MHz	F	35
14 - 23.99 MHz	F	25
24 - 25 MHz	F / 3	25 / 50
25 - 30 MHz	F / 3	25 / 50
30 - 75 MHz	3	50
75 - 125 MHz	5	80
125 - 150 MHz	5	100
150 - 200 MHz	5	120

Part Number Table

Case	Frequency (MHz)	Frequency Tolerance (PPM)	Temperature Stability (PPM)	Temperature Range 60 = -10 to +60 70 = -20 to +70	Load Capacitance pf 00 = Series	Vibration Mode AT Cut F = Fund 0.3 Overtone	Ant Part Number
HC49U	1.8432	20	50	60	30	ATF	XTL-1012
HC49U	2	50	100	60	20	ATF	XTL-1014
HC49U	2.4576	20	50	60	30	ATF	XTL-1017
HC49U	3.2768	20	30	60	12	ATF	XTL-1020
HC49U	3.579545	20	50	60	20	ATF	XTL-1021
HC49U	3.6864	20	50	60	30	ATF	XTL-1023
HC49U	3.6864	30	50	70	30	ATF	XTL-1024
HC49U	4	20	10	70	30	ATF	XTL-1027
HC49U	4	20	50	60	30	ATF	XTL-1028
HC49U	4	30	50	70	30	ATF	XTL-1029
HC49U	4.096	20	20	70	30	ATF	XTL-1031
HC49U	4.096	30	50	70	30	ATF	XTL-1032
HC49U	4.194304	20	30	60	12	ATF	XTL-1033
HC49U	4.608	20	50	60	30	ATF	XTL-1037

Part Number Table

Case	Frequency (MHz)	Frequency Tolerance (PPM)	Temperature Stab (PPM)	Temperature Range 60 = -10 to +60 70 = -20 to +70	Load Capacitance pf 00 = Series	Vibration Mode AT Cut F = Fund 0.3 Overtone	Ant Part Number
HC49U	4.9152	20	50	60	30	ATF	XTL-1040
HC49U	4.9152	30	50	70	30	ATF	XTL-1041
HC49U	5	20	50	60	30	ATF	XTL-1043
HC49U	5.0688	20	50	60	0	ATF	XTL-1044
HC49U	6	20	50	60	30	ATF	XTL-1051
HC49U	6	30	50	70	30	ATF	XTL-1053
HC49U	6.144	20	50	60	30	ATF	XTL-1055
HC49U	6.5536	20	30	60	12	ATF	XTL-1057
HC49U	7.3728	20	50	60	30	ATF	XTL-1059
HC49U	8	20	50	60	30	ATF	XTL-1062
HC49U	8	30	50	70	30	ATF	XTL-1064
HC49U	10	20	10	70	30	ATF	XTL-1069
HC49U	10	20	50	60	30	ATF	XTL-1070
HC49U	11	20	30	60	30	ATF	XTL-1073
HC49U	11.0592	20	30	60	20	ATF	XTL-1074
HC49U	12	20	30	60	30	ATF	XTL-1079
HC49U	12.288	20	50	60	30	ATF	XTL-1081
HC49U	14.31818	20	50	60	0	ATF	XTL-1083
HC49U	14.7456	20	30	60	30	ATF	XTL-1087
HC49U	16	20	30	60	30	ATF	XTL-1089
HC49U	19.6608	20	50	60	30	ATF	XTL-1096
HC49U	20	20	30	60	0	ATF	XTL-1098
HC49U	22.1184	20	50	60	30	ATF	XTL-1114
HC49U	24	20	50	60	0	ATF	XTL-1120
HC49U	32	20	30	60	0	ATF	XTL-1131


HC-49/SM



Features and Applications:

Designed for applications where board height is critical

- General, industrial, microcontrollers
- Cost effective
- Surface mount
- Low profile (4 mm height)
- Superior resistance weld HC49/4SMX metal case
- Supplied taped and reeled



Dimensions : Millimetres

Specification Table

Nominal Frequency Range	3.5 to 32 MHz	24 to 70 MHz
Vibration Mode	Fundamental (AT)	3rd Overtone (AT)
Frequency Tolerance at 25°C	±20, ±30 or ±50 ppm (Options : ±10, ±15 ppm)	
Temperature Stability	±30 or ± 50 ppm	
Operating Temperature Range	-10°C to +60°C or -20°C to +70°C	
Storage Temperature Range	-20°C to +70°C or -30°C to +80°C	
Load Capacitance	8 pF to 33 pF or series	
Equivalent Series Resistance	See ESR table below	
Shunt Capacitance	5 pF maximum (≤18 MHz) or 7 pF maximum (>18 MHz)	
Drive Level	200 µW maximum (≤5 MHz) 100 µW maximum (>5 MHz)	
Insulation Resistance	500 MΩ minimum at 100 V dc	
Aging	±5 ppm per year	

ESR Table

Case	Vibration	HC 49SM
Frequency	Mode	Ω Maximum
3.5 - 3.99 MHz	F	150
4 - 4.99 MHz	F	120
5 - 5.99 MHz	F	100
6 - 6.99 MHz	F	80
7 - 7.99 MHz	F	80

ESR Table

Case	Vibration	HC 49SM
Frequency	Mode	Ω Maximum
8 - 9.99 MHz	F	70
10 - 13.99 MHz	F	50
14 - 23.99 MHz	F	40
24 - 25 MHz	F / 3	40 / 80
25 - 30 MHz	F / 3	40 / 80
30 - 70 MHz	3	80

Part Number Table

Case	Frequency (MHz)	Frequency Tolerance (PPM)	Temperature Stability (PPM)	Temperature Range 60 = -10 to +60 70 = -20 to +70	Load Capacitance pf 00 = Series	Vibration Mode AT Cut F = Fund 0.3 Overtone	Ant Part Number
HC49SM	3.579545	30	50	60	16	ATF	XTL-5014
HC49SM	3.6864	30	50	60	16	ATF	XTL-5014
HC49SM	4	30	50	60	16	ATF	XTL-5021
HC49SM	4.9152	30	50	60	16	ATF	XTL-5025
HC49SM	6	30	50	60	30	ATF	XTL-5032
HC49SM	8	30	50	60	16	ATF	XTL-5038
HC49SM	10	30	50	60	16	ATF	XTL-5043
HC49SM	11.0592	30	50	60	16	ATF	XTL-5048
HC49SM	12	30	50	60	16	ATF	XTL-5050
HC49SM	16	30	50	60	16	ATF	XTL-5055
HC49SM	20	30	50	60	16	ATF	XTL-5062

HC-49/S




Features and Applications:

Designed for applications where board height space is critical

- General, industrial, microcontrollers
- Cost effective
- Surface mount
- Low profile (4 mm height)
- Superior resistance weld HC49/4H metal case

Supplied loose as standard. Taped product available to special order



Dimensions : Millimetres

Specification Table

Nominal Frequency Range	3.5 to 32 MHz	24 to 70 MHz
Vibration Mode	Fundamental (AT)	3rd Overtone (AT)
Frequency Tolerance at 25°C	± 20 , ± 30 or ± 50 ppm (Options : ± 10 , ± 15 ppm)	
Temperature Stability	± 30 or ± 50 ppm	
Operating Temperature Range	-10°C to $+60^{\circ}\text{C}$ (Option : -20°C to $+70^{\circ}\text{C}$)	
Storage Temperature Range	-20°C to $+70^{\circ}\text{C}$ (Option : -30°C to $+80^{\circ}\text{C}$)	
Load Capacitance	8 pF to 32 pF or series	
Equivalent Series Resistance	See ESR table below	
Shunt Capacitance	5 pF maximum (≤ 18 MHz) or 7 pF maximum (> 18 MHz)	
Drive Level	200 μW maximum (≤ 5 MHz) 100 μW maximum (> 5 MHz)	
Insulation Resistance	500 M Ω minimum at 100 V dc	
Aging	± 5 ppm per year	


ESR Table

Case	Vibration	HC 49S
Frequency	Mode	Ω Maximum
3.5 - 3.99 MHz	F	150
4 - 4.99 MHz	F	120
5 - 5.99 MHz	F	100
6 - 6.99 MHz	F	80
7 - 7.99 MHz	F	80
8 - 9.99 MHz	F	70
10 - 13.99 MHz	F	50
14 - 23.99 MHz	F	40
24 - 25 MHz	F / 3	40 / 80
25 - 30 MHz	F / 3	40 / 80
30 - 70 MHz	3	80

Part Number Table


Case	Frequency (MHz)	Frequency Tolerance (PPM)	Temperature Stability (PPM)	Temperature Range 60 = -10 to +60 70 = -20 to +70	Load Capacitance pf 00 = Series	Vibration Mode AT Cut F = Fund 0.3 Overtone	Ant Part Number
HC49S	3.579545	30	50	70	20	ATF	XTL-3012
HC49S	3.6864	30	50	70	30	ATF	XTL-3015
HC49S	4	20	50	60	30	ATF	XTL-3018
HC49S	4.194304	30	50	60	30	ATF	XTL-3024
HC49S	4.433619	30	50	60	20	ATF	XTL-3026
HC49S	4.9152	30	50	70	30	ATF	XTL-3028
HC49S	6	30	50	60	30	ATF	XTL-3035
HC49S	7.3728	15	30	60	18	ATF	XTL-3039
HC49S	7.68	30	50	60	30	ATF	XTL-3042
HC49S	8	30	50	70	30	ATF	XTL-3044
HC49S	9.8304	30	50	60	30	ATF	XTL-3048
HC49S	10	30	50	70	30	ATF	XTL-3052
HC49S	11.0592	30	50	70	30	ATF	XTL-3060
HC49S	12	30	50	70	30	ATF	XTL-3064
HC49S	16	30	50	70	30	ATF	XTL-3069
HC49S	18.432	30	50	60	30	ATF	XTL-3074
HC49S	20	30	50	70	12	ATF	XTL-3078
HC49S	24	50	50	60	30	ATF	XTL-3085

DX-57



Features and Applications:

- Communication Equipment, PDA's, Wireless security systems
- Cost effective
- Surface mount
- Ultra thin ceramic package
- Height 1.4 mm maximum
- Supplied taped and reeled



Specification Table

Nominal Frequency Range	10 to 30 MHz	30 to 60 MHz
Vibration Mode	Fundamental (AT)	3rd Overtone (AT)
Frequency Tolerance at 25°C	±20, ±30 or ±50 ppm	
Temperature Stability	±30 or ± 50 ppm	
Operating Temperature Range	-20°C to +70°C	
Storage Temperature Range	-30°C to +80°C	
Load Capacitance	8 pF to 32 pF or series	
Equivalent Series Resistance	See ESR table below	
Shunt Capacitance	7 pF maximum	
Drive Level	100 µW maximum	
Insulation Resistance	500 MΩ minimum at 100 V dc	
Aging	±5 ppm per year	

ESR Table

Case	Vibration	DX-57
Frequency	Mode	Ω Maximum
10 - 13.99 MHz	F	60
14 - 30 MHz	F	50
30 - 60 MHz	3	100

Part Number Table

Case	Frequency (MHz)	Frequency Tolerance (PPM)	Temperature Stability (PPM)	Temperature Range 60 = -10 to +60 70 = -20 to +70	Load Capacitance pf 00 = Series	Vibration Mode AT Cut F = Fund 0.3 Overtone	Ant Part Number
DX57	10	30	50	70	20	ATF	XTL-7024
DX57	11.0592	30	50	70	20	ATF	XTL-7026
DX57	12	30	50	70	20	ATF	XTL-7029
DX57	18.432	30	50	70	20	ATF	XTL-7036
DX57	19.6608	30	50	70	20	ATF	XTL-7040
DX57	24	30	50	70	20	ATF	XTL-7047
DX57	27	30	50	70	20	ATF	XTL-7052
DX57	32	30	50	70	20	AT3	XTL-7056

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.