


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	1/11/10	D.GRIFFIN
B	ECN 5123: ADDED DESCRIPTIONS, CHANGED "J1" TO "P2" IN WIRE MAP	11/4/10	D.FRISIELLO
C	ECN 5868: ADDED LENGTHS 03 M, 075 M	12/1/11	D.FRISIELLO
D	ECN6237: ADDED CONTACT PLATING NOTE. UPDATED FORMAT.	09/18/12	DFP



PART NO.	LENGTH METERS, [FT]
CAUALB-03M	0.3 [.98]
CAUALB-05M	0.5 [1.64]
CAUALB-075M	0.75 [2.46]
CAUALB-1M	1.0 [3.28]
CAUALB-2M	2.0 [6.56]
CAUALB-3M	3.0 [9.84]
CAUALB-4M	4.0 [13.12]
CAUALB-5M	5.0 [16.40]

NOTES:

- CABLE ASSEMBLY SHALL HAVE 360° SHIELD TERMINATION.
- CABLE ASSEMBLY SHALL MEET USB 2.0 REQUIREMENTS.
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: 012 [305] = +1 [25] / -0 >12 [305] 060 [1524] = +2 [51] / -0 >60 [1524] 0120 [3048] = +4 [102] / -0 >120 [3048] 0300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = N .2 .XX = N .02 .XXX = N .005	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845			
	DRAWN BY D.FRISIELLO	10/23/09				
	CHECKED BY M.MARTINEZ	10/23/09	CATEGORY	USB		
	APPROVED BY S.SMITH	10/23/09	PRODUCT DESCRIPTION			
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CA, USB TYPE A-M LATCH/TYPE B-M			
PROJECTION 	COLOR VARIATIONS MAY OCCUR		SIZE	FSCM NO.	DWG. NO.	REV.
			A	43321	CAUALB	D
			SCALE: NONE	CAD FILE: CAUALB.SLDDRW		SHEET 1 OF 1