


USB Connector A Type Receptacle Right Angle Single Deck (SMT)

154-UAR42

KOBICONN

USB Connector A Type Receptacle Right Angle Single Deck (SMT)



Dimensions: mm

Electrical Specifications

Contact Resistance:	30 Milliohms max.
Dielectric w/standing Voltage:	750 VAC
Insulator Resistance:	1,000 Megaohms min.
Current Rating:	1.0 Ampere max. @ 30°C
Durability:	1500 Cycles
Temperature Range:	-55°C to +85°C
Voltage:	30 VAC

SPECIFICATIONS

Part Name	Item	Qty.	Material
Contacts:	3	4	Copper Alloy/Selective Gold Plating: 2 - $A\mu 5\mu$ "; 5 - $A\mu 30\mu$ "
Housing:	2	1	Thermoplastic, Glass filled, 240°C
Shell:	1	1	Copper Alloy/ Tin-Lead Plated over Copper

Date Last Revised: 5-26-06

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300184

154-UAR42

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[154-UAR42](#)