



3M™ Chemicals for Electronics Markets

Products

- Aerosol Cleaners
- + Battery Materials
- Electronic Liquids
- Electronic Coatings
- Electronic Surfactants
- Engineered Fluids
- 1230 Fire Protection Fluid
- Organic Electronics
- Performance Fluids
- Specialty Gases

Solutions

- Aerospace
- Archives & Museums Fire Protection
- Automotive & Transportation
- Data Processing & Control Rooms
- Electronics
- Fire Protection
- Hard Disk Drive
- Marine
- Medical Devices
- Military
- Museum & Preservation
- Oil & Gas
- Precision Optics
- Semiconductor
- Telecommunications

Resources

- Contact Us
- MSDS
- 3M RoHS/REACH Declaration
- Tech Support
- Technical Documents and Literature
- Where to Buy

Product Catalog for

>

Electrical Products

>

Wire Fasteners

>

Cable Ties

>

Cable Ties

>

3M™ Plain Cable Tie PB8NT50-M

Printer-friendly format

The 3M™ Plain Cable Tie PB8NT50-M is 8" in length. Natural color. 50 lb tensile strength. 1000 per bag. (Replaces product number: 41938)

3M Id : 80-6114-7003-2

GTIN(UPC/EAN) : 0 00 51128 59344 8

Characteristics

|                                            |                       |
|--------------------------------------------|-----------------------|
| Agency Approvals                           | UL                    |
| Cable Length                               | 7.6 Inch              |
| Cable Length (mm)                          | 193.04 mm             |
| Color                                      | Natural               |
| Country of Origin                          | USA                   |
| EU RoHS Compliant                          | Yes                   |
| Indoor/Outdoor                             | Indoor                |
| Maximum Bundle Diameter                    | 2 Inch                |
| Maximum Bundle Diameter (mm)               | 50.8 mm               |
| Maximum Operating Temperature              | 85 Degree Celsius     |
| Maximum Operating Temperature (Celsius)    | 85 Degree Celsius     |
| Maximum Operating Temperature (Fahrenheit) | 185 Degree Fahrenheit |
| Mil Spec                                   | MS3367-1-9            |
| Minimum Bundle Diameter                    | 0.0625 Inch           |
| Minimum Bundle Diameter (mm)               | 1.6 mm                |
| Tensile Strength                           | 50 Pound              |
| Tensile Strength (kg)                      | 22.67962 Kilogram     |
| Thickness                                  | 0.054 Inch            |
| Thickness (mm)                             | 1.4 mm                |
| Width                                      | 0.18 Inch             |
| Width (mm)                                 | 4.6                   |

