

MICRO SWITCH

A DIVISION OF HONEYWELL-INTERNATIONAL, INC. MILWAUKEE, WISCONSIN

FED. MFR. CODE 91929

SWITCH - BASIC


CATALOG LISTING

6AS5


(M) 6AS5 ISSUE 1
 REPLACES
6AS5
 DRAWING NUMBER
M
 ISSUE
28
6
 REVISIONS

A	CO 8520	K.F.M.	6 NOV. 56
B	0022234	M.B.F.	18 DEC 66
C	0025310	M.B.S.	23 JAN 69
D	42511	T.M.M.	19 FEB 79
E	CO-73287-J	J.A.L.	22 NOV 93


 CHECK
 G.C.H. 7 NOV. 56
 G.C.H. 9 NOV. 56
 G.C.H. 6 NOV. 56
 DRAWN
 K.F.M. 6 NOV. 56
 FO-90378



CORROSION RESISTANT STEEL LEAF



6X 6-32 UNC X (.219)
 BINDING HEAD COMBINATION
 TERMINAL SCREW AND
 CUPWASHER



NOTE -

1-SWITCHES OPERATE WITHIN .030 (MOTION AT END OF LEAF) OF EACH OTHER.

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

DO NOT OVERTRAVEL MORE THAN .060
 OVERTRAVEL ----- .030 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
 (2) S.P.D.T.

UNDERWRITERS' LAB. INC. LISTED RATINGS
 -L95- 15 A - 125, 250, OR 480 VAC
 1/2 A - 125 VDC; 1/4 A - 250 VDC
 1/8 HP - 125 VAC; 1/4 HP - 250 VAC

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED
 DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
 ONE PLACE (.0) ±.030
 TWO PLACE (.00) ±.015
 THREE PLACE (.000) ±.005
 ANGLES ±

WEIGHT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[6AS5](#)