




1 2 3 4 5

A B C D E F G H

ALL DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC. U.S. PATENT OFFICE. NO REPRODUCTION, COPIED, OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.



488-148-505-D	121-810-022	14.0 FT (4.3 M)	50.0 IN (1270.0 MM)	WHITE
488-148-504-D	121-810-012	14.0 FT (4.3 M)	50.0 IN (1270.0 MM)	BLACK
488-148-503-D	121-810-002	14.0 FT (4.3 M)	50.0 IN (1270.0 MM)	SILVER SATIN
488-108-502-D	121-810-021	10.0 FT (3.0 M)	42.0 IN (1066.8 MM)	WHITE
488-108-501-D	121-810-011	10.0 FT (3.0 M)	42.0 IN (1066.8 MM)	BLACK
488-108-500-D	121-810-001	10.0 FT (3.0 M)	42.0 IN (1066.8 MM)	SILVER SATIN
488-078-505-D	121-810-020	7.0 FT (2.1 M)	28.0 IN (711.2 MM)	WHITE
488-078-504-D	121-810-010	7.0 FT (2.1 M)	28.0 IN (711.2 MM)	BLACK
488-078-503-D	121-810-000	7.0 FT (2.1 M)	28.0 IN (711.2 MM)	SILVER SATIN
488-058-502-D	121-810-023	5.0 FT (1.5 M)	22.0 IN (558.8 MM)	WHITE
488-058-501-D	121-810-013	5.0 FT (1.5 M)	22.0 IN (558.8 MM)	BLACK
488-058-500-D	121-810-003	5.0 FT (1.5 M)	22.0 IN (558.8 MM)	SILVER SATIN
IOI PART NUMBER	IOI CABLE PART NUMBER	EXTENDED LENGTH "X"	RETRACTED LENGTH "R"	

TABULATION BLOCK

TABULATION BLOCK

CUSTOMER APPROVAL
ENGR. SIGN *Matt Lerner*
DATE: 4-13-99

- NOTES: UNLESS OTHERWISE SPECIFIED.
1. TEST CABLE FOR ALL OPENS & SHORTS.
 2. PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

2	"X" FT	IOI	SEE "TABULATION BLOCK"	MODULAR COIL CABLE, 26 AWG (7/34) BARE COPPER, 8 CONDUCTOR, UNSHIELDED, PVC JACKET, (SEE TABULATION BLOCK FOR COLOR).
1	2 PCS	IOI	325-881-50X	CONNECTOR, MODULAR PLUG, 8 POSITION, 8 CONDUCTOR, 50U" AU, FLAT TYPE EXIT.
ITEM	QTY	MFG.	IOI PART NO.	DESCRIPTION
CABLE ASSEMBLY PARTS LIST				

THIRD ANGLE PROJECTION

UNLESS OTHERWISE NOTED:
1) DIMENSIONS ARE IN INCHES (MILLIMETERS)
2) TOLERANCES:
XX ± 0.25 (6.35)

I/O INTERCONNECT
SANTA ANA, CALIFORNIA

TITLE: 8P8C/8P8C COIL CABLE, REVERSE STYLE, CABLE ASSEMBLY

REV. 1

REV. 2

SCALE: NONE


SHEET 1 OF 1

A B C D E F G H


THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC. NO PARTS SHALL BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT THE WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.

REV.	ZONE	DESCRIPTION	DATE	APPROVED
X1		XXB-502-D	03/24/99	E.V.

1



2



3



CUSTOMER APPROVAL

ENGR. SIGN Math. Neme
DATE: 4-12-99

NOTES: UNLESS OTHERWISE SPECIFIED.

1. CABLE TO BE BUNDLED AND TWIST TIED.
2. TEST CABLE FOR ALL OPENS & SHORTS.
3. PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

5


ITEM	QTY	MFG.	IDI PART NO.	DESCRIPTION
2	*X	IDI	120-810-020	MODULAR CABLE, 26 AVG (7/34) BARE COPPER, 8 CONDUCTOR, UNSHIELDED, WHITE PVC.
1	2 PCS	IDI	325-881-50X	CONNECTOR, MODULAR PLUG, 8 POSITION, 8 CONDUCTOR, 50u" AU, FLAT TYPE EXIT.

CABLE ASSEMBLY PARTS LIST

H2881-25-ND
H2881-14 ND
H2881-07-ND

488-258-502-D	25.0 FT ± 4.0 IN 7.62 M ± 101.6 MM
488-148-502-D	14.0 FT ± 3.0 IN 4.27 M ± 76.2 MM
488-078-502-D	7.0 FT ± 2.0 IN 2.13 M ± 50.8 MM
PART NUMBER	LENGTH *X*


I/O INTERCONNECT	
SANTA ANA, CALIFORNIA	
DATE	REV.
03/24/99	X1



THIRD ANGLE PROJECTION
UNLESS OTHERWISE NOTED:
1) DIMENSIONS ARE IN INCHES (MILLIMETERS)
2) TOLERANCES
XXX ± 0.25 (6.35)

TITLE	
BPBP MODULAR, REVERT STYLE, WHITE, CABLE ASSEMBLY	
PART NO.	488-XXB-502-D
DRAWN	488-XXB-502-D
CHECKED	DIGI KEY
SCALE	NONE
SHEET	1 OF 1

A B C D E F G H
 DWG. NO. ZONE REV. DESCRIPTION DATE APPROVED
 XXB-510-D XI 1 CUSTOMER APPROVAL 03/24/99 E.V.



CUSTOMER APPROVAL

ENGR. SIGN Matt Jones
 DATE: 4-12-99

NOTES: UNLESS OTHERWISE SPECIFIED.

1. CABLE TO BE BUNDLED AND TWIST TIED.
2. TEST CABLE FOR ALL OPENS & SHORTS.
3. PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

488-258-510-D	25.0 FT ± 4.0 IN 7.62 M ± 101.6 MM
488-148-510-D	14.0 FT ± 3.0 IN 4.27 M ± 76.2 MM
488-078-510-D	7.0 FT ± 2.0 IN 2.13 M ± 50.8 MM
PART NUMBER	LENGTH "X"

I/O INTERCONNECT
SANTA ANA, CALIFORNIA

THIRD ANGLE PROJECTION

UNLESS OTHERWISE NOTED:
 1) DIMENSIONS ARE IN INCHES (MILLIMETER)
 2) TOLERANCES:
 XXX ± 0.25 (6.35)

SCALE: NONE SHEET 1 OF 1

ITEM	QTY	MFG.	IOI PART NO.	DESCRIPTION
2	"X"	IOI	120-810-000	MODULAR CABLE, 26 AWG (7/34) BARE COPPER, 8 CONDUCTOR, UNSHIELDED, SILVER SATIN PVC.
1	2 PCS	IOI	325-881-50X	CONNECTOR, MODULAR PLUG, 8 POSITION, 8 CONDUCTOR, 50u" AU, FLAT TYPE EXIT.

CABLE ASSEMBLY PARTS LIST


A B C D E F G H

THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC., U.S.A. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.

DWG. NO.	ZONE	REV.	DESCRIPTION	DATE	APPROVED
XX8-511-D		X1	CUSTOMER APPROVAL	03/24/99	E.V.

WIRE DIAGRAM

P1		P2
1	GRAY	8
2	ORANGE	7
3	BLACK	6
4	RED	5
5	GREEN	4
6	YELLOW	3
7	BLUE	2
8	BROWN	1



CUSTOMER APPROVAL
ENGR. SIGN Math Nemec
DATE: 4-12-99

NOTES: UNLESS OTHERWISE SPECIFIED.

1. CABLE TO BE BUNDLED AND TWIST TIED.
2. TEST CABLE FOR ALL OPENS & SHORTS.
3. PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG.
PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.


488-259-511-D	25.0 FT ± 4.0 IN 7.62 M ± 101.6 MM
488-148-511-D	14.0 FT ± 3.0 IN 4.27 M ± 76.2 MM
488-078-511-D	7.0 FT ± 2.0 IN 2.13 M ± 50.8 MM

PART NUMBER	LENGTH "X"
I/O INTERCONNECT	



REV.	DATE	BY	CHKD.	APP'D.


TITLE	BP8P MODULAR, STANDARD STYLE, BLACK, CABLE ASSEMBLY
PART NO.	488-XX8-511-D
DWG. NO.	488-XX8-511-D
CUSTOMER	DIGI KEY
SCALE	NONE
SHEET	1 OF 1



THIRD ANGLE PROJECTION
UNLESS OTHERWISE NOTED:
1) DIMENSIONS ARE IN INCHES (MILLIMETER)
2) TOLERANCES:
X.XX ± 0.25 (6.35)

ITEM	QTY	MFG.	IOI PART NO.	DESCRIPTION
2	*X*	IOI	120-810-010	MODULAR CABLE, 26 AWG (7/34) BARE COPPER, 8 CONDUCTOR, UNSHIELDED, BLACK PVC.
1	2 PCS	IOI	325-881-50X	CONNECTOR, MODULAR PLUG, 8 POSITION, 8 CONDUCTOR, 50u" Au, FLAT TYPE EXIT.

CABLE ASSEMBLY PARTS LIST



CUSTOMER APPROVAL
ENGR. SIGN Math Amec
DATE: 4-12-99

- NOTES: UNLESS OTHERWISE SPECIFIED.
- CABLE TO BE BUNDLED AND TWIST TIED.
 - TEST CABLE FOR ALL OPENS & SHORTS.
 - PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG.
PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

2	*X*	101	120-810-010	MODULAR CABLE, 26 AWG (7/34) BARE COPPER, 8 CONDUCTOR, UNSHIELDED, BLACK PVC.
1	2 PCS	101	325-881-50X	CONNECTOR, MODULAR PLUG, 8 POSITION, 8 CONDUCTOR, 50u" AW, FLAT TYPE EXIT.
ITEM	QTY	MFG.	IOI PART NO.	DESCRIPTION

CABLE ASSEMBLY PARTS LIST

488-258-501-D	25.0 FT ± 4.0 IN 7.62 M ± 101.6 MM
488-148-501-D	14.0 FT ± 3.0 IN 4.27 M ± 76.2 MM
488-078-501-D	7.0 FT ± 2.0 IN 2.13 M ± 50.8 MM
PART NUMBER I/O INTERCONNECT	LENGTH *X*

THIRD ANGLE PROJECTION

UNLESS OTHERWISE NOTED:
1) DIMENSIONS ARE IN INCHES (MILLIMETER)
2) TOLERANCES:
XXX ± 0.25 (6.35)

I/O INTERCONNECT

SANTA ANA, CALIFORNIA

TITLE: BP8P MODULAR, REVERT STYLE, BLACK, CABLE ASSEMBLY

REV. NO. 488-XXB-501-D

DWG. NO. 488-XXB-501-D

CUSTOMER DIGI KEY

SCALE NONE


SHEET 1 OF 1

THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC. NO PARTS OR SUBASSEMBLIES MAY BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.

A		B		C		D		E		F		G		H	
DWG. NO.		ZONE		REV.		DESCRIPTION		DATE		CUSTOMER APPROVAL		APPROVED		E.V.	
XXB-500-D				X1											

WIRE DIAGRAM

P1	P2
1	GRAY
2	ORANGE
3	BLACK
4	RED
5	GREEN
6	YELLOW
7	BLUE
8	BROWN



CUSTOMER APPROVAL

ENGR. SIGN Matt Jensen

DATE: 4-17-99


NOTES: UNLESS OTHERWISE SPECIFIED.

1. CABLE TO BE BUNDLED AND TWIST TIED.

2. TEST CABLE FOR ALL OPENS & SHORTS.

3. PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG.
PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

THIRD ANGLE PROJECTION



UNLESS OTHERWISE NOTED:
1) DIMENSIONS ARE IN INCHES (MILLIMETER)
2) TOLERANCES:
XXX ± 0.25 (6.35)

MODULAR CABLE, 26 AWG (7/34) BARE COPPER, 8 CONDUCTOR, UNSHIELDED,
SILVER SATIN PVC.

CONNECTOR, MODULAR PLUG, 8 POSITION, 8 CONDUCTOR, 50U" AU, FLAT TYPE EXIT.

DESCRIPTION

CABLE ASSEMBLY PARTS LIST

ITEM	QTY	MFG.	IOI PART NO.	DESCRIPTION
2	2 PCS	IOI	120-810-000	MODULAR CABLE, 26 AWG (7/34) BARE COPPER, 8 CONDUCTOR, UNSHIELDED, SILVER SATIN PVC.
1	2 PCS	IOI	325-881-50X	CONNECTOR, MODULAR PLUG, 8 POSITION, 8 CONDUCTOR, 50U" AU, FLAT TYPE EXIT.
CABLE ASSEMBLY PARTS LIST				
PART NUMBER				
I/O INTERCONNECT				
LENGTH 'X'				
TITLE				
SANTA ANA, CALIFORNIA				
BPPB MODULAR, REVERT STYLE, SILVER SATIN, CABLE ASSEMBLY				
PART NO. 488-XXB-500-D				
PVG NO. 488-XXB-500-D				
CUSTOMER DIGI KEY				
REV. X1				
SCALE: NONE				
SHEET 1 OF 1				

H2883-25-ND

H2883-14-ND

H2883-07-ND

488-258-500-D

250 FT ± 4.0 IN

7.62 M ± 101.6 MM

488-148-500-D

14.0 FT ± 3.0 IN

4.27 M ± 76.2 MM

488-078-500-D

7.0 FT ± 2.0 IN

2.13 M ± 50.8 MM

PART NUMBER

I/O INTERCONNECT

LENGTH 'X'

TITLE

SANTA ANA, CALIFORNIA

BPPB MODULAR, REVERT STYLE, SILVER SATIN, CABLE ASSEMBLY

PART NO. 488-XXB-500-D

PVG NO. 488-XXB-500-D

CUSTOMER DIGI KEY

REV. X1



SCALE: NONE

SHEET 1 OF 1

A		B	C	D	E	F	G	H
DWG. NO.		ZONE	REV.	DESCRIPTION	DATE	APPROVED		
XXB-521-D			X1	CUSTOMER APPROVAL	03/24/99	E.V.		

THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC. AND ARE NOT TO BE REPRODUCED OR USED IN ANY MANNER WITHOUT THE WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.

1



1 2 PCS

P1

OPEN END

WIRE DIAGRAM

P1	OPEN END
1	GRAY
2	ORANGE
3	BLACK
4	RED
5	GREEN
6	YELLOW
7	BLUE
8	BROWN

3



CUSTOMER APPROVAL
ENGR. SIGN Math Nemes
DATE: 4-12-99

H3882-25-ND
H3882-14-ND
H3882-07-ND


NOTES: UNLESS OTHERWISE SPECIFIED.

- CABLE TO BE BUNDLED AND TWIST TIED.
- TEST CABLE FOR ALL OPENS & SHORTS.
- PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

488-258-521-D	25.0 FT ± 4.0 IN 7.62 M ± 101.6 MM
488-148-521-D	14.0 FT ± 3.0 IN 4.27 M ± 76.2 MM
488-078-521-D	7.0 FT ± 2.0 IN 2.13 M ± 50.8 MM

PART NUMBER
I/O INTERCONNECT

THIRD ANGLE PROJECTION



I/O INTERCONNECT

SANTA ANA, CALIFORNIA

REV.	DATE	BY	DESCRIPTION
1			8P8P MODULAR TO OPEN END BLACK, CABLE ASSEMBLY
2			488-XXB-521-D
3			488-XXB-521-D
4			DIGI KEY
5			SCALE: NONE
6			SHEET 1 OF 1

MODULAR CABLE, 26 AWG (7/34) BARE COPPER, 8 CONDUCTOR, UNSHIELDED, BLACK PVC.

CONNECTOR, MODULAR PLUG, 8 POSITION, 8 CONDUCTOR, 50u" AU, FLAT TYPE EXIT.

DESCRIPTION


CABLE ASSEMBLY PARTS LIST

5

ITEM	QTY	MFG.	IDT PART NO.	DESCRIPTION
2			120-810-010	
1	1 PC		325-881-50X	

A	B	C	D	E	F	G	H
DATE	REV.	DESCRIPTION	DATE	APPROVED			
XXB-522-D	X1	CUSTOMER APPROVAL	03/24/99	E.V.			

THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC. ALL RIGHTS ARE RESERVED. NO PART OF THIS DOCUMENT SHALL BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT THE WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.



WIRE DIAGRAM

P1	OPEN END
1	GRAY
2	ORANGE
3	BLACK
4	RED
5	GREEN
6	YELLOW
7	BLUE
8	BROWN

CUSTOMER APPROVAL
 ENGR. SIGN Math Amec
 DATE: 4-12-99

- NOTES: UNLESS OTHERWISE SPECIFIED.
- CABLE TO BE BUNDLED AND TWIST TIED.
 - TEST CABLE FOR ALL OPENS & SHORTS.
 - PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

ITEM	QTY	MFG.	IOI PART NO.	DESCRIPTION
2	1 PC	IOI	120-810-020	MODULAR CABLE, 26 AVG (7/34) BARE COPPER, 8 CONDUCTOR, UNSHIELDED, WHITE PVC.
1	1 PC	IOI	325-881-50X	CONNECTOR, MODULAR PLUG, 8 POSITION, 8 CONDUCTOR, 50U" AU, FLAT TYPE EXIT.



THIRD ANGLE PROJECTION
 UNLESS OTHERWISE NOTED:
 1) DIMENSIONS ARE IN INCHES (MILLIMETER)
 2) TOLERANCES:
 XXX ± 0.25 (6.35)

CABLE ASSEMBLY PARTS LIST


488-258-522-D	25.0 FT ± 4.0 IN 7.62 M ± 101.6 MM
488-148-522-D	14.0 FT ± 3.0 IN 4.27 M ± 76.2 MM
488-078-522-D	7.0 FT ± 2.0 IN 2.13 M ± 50.8 MM
PART NUMBER	LENGTH "X"
I/O INTERCONNECT	
TITLE	SANTA ANA, CALIFORNIA
DATE	03/24/99
REV.	X1
CUSTOMER	DIGI KEY
SCALE	NONE
SHEET	1 OF 1



BPBP MODULAR TO OPEN END	WHITE, CABLE ASSEMBLY
PART NO.	488-XXB-522-D
REV.	03/24/99
CUSTOMER	DIGI KEY
SCALE	NONE
SHEET	1 OF 1

A		B	C	D	E	F	G	H
DWG. NO.		ZONE	REV.	DESCRIPTION		DATE		APPROVED
XXB-51X-D			X1	CUSTOMER APPROVAL		03/26/99		E.V.
			X2	ADD RETRACTED LENGTH		03/29/99		E.V.

THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC., U.S.A. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.




CUSTOMER APPROVAL
ENGR. SIGN Math Lemmer
DATE: 4-13-99

- NOTES: UNLESS OTHERWISE SPECIFIED.
1. TEST CABLE FOR ALL OPENS & SHORTS.
 2. PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

488-148-515-D	121-810-022	14.0 FT (4.3 M)	50.0 IN (1270.0 MM)	WHITE
488-148-514-D	121-810-012	14.0 FT (4.3 M)	50.0 IN (1270.0 MM)	BLACK
488-148-513-D	121-810-002	14.0 FT (4.3 M)	50.0 IN (1270.0 MM)	SILVER SATIN
488-108-512-D	121-810-021	10.0 FT (3.0 M)	42.0 IN (1066.8 MM)	WHITE
488-108-511-D	121-810-011	10.0 FT (3.0 M)	42.0 IN (1066.8 MM)	BLACK
488-108-510-D	121-810-001	10.0 FT (3.0 M)	42.0 IN (1066.8 MM)	SILVER SATIN
488-078-515-D	121-810-020	7.0 FT (2.1 M)	28.0 IN (711.2 MM)	WHITE
488-078-514-D	121-810-010	7.0 FT (2.1 M)	28.0 IN (711.2 MM)	BLACK
488-078-513-D	121-810-000	7.0 FT (2.1 M)	28.0 IN (711.2 MM)	SILVER SATIN
488-058-512-D	121-810-023	5.0 FT (1.5 M)	22.0 IN (558.8 MM)	WHITE
488-058-511-D	121-810-013	5.0 FT (1.5 M)	22.0 IN (558.8 MM)	BLACK
488-058-510-D	121-810-003	5.0 FT (1.5 M)	22.0 IN (558.8 MM)	SILVER SATIN
101 PART NUMBER	101 CABLE PART NUMBER	EXTENDED LENGTH "X"	RETRACTED LENGTH "R"	

TABULATION BLOCK

8					BROWN		1		THIRD ANGLE PROJECTION								I/O INTERCONNECT		SANTA ANA, CALIFORNIA	
2		*X" FT		101		SEE "TABULATION BLOCK"		MODULAR COIL CABLE, 26 AWG (7/34) BARE COPPER, 8 CONDUCTOR, UNSHIELDED, PVC JACKET, (SEE TABULATION BLOCK FOR COLOR).		DRAWING NO. 8PBC/8PBC		REV. 000000		TITLE		8PBC/8PBC COIL CABLE, STANDARD STYLE, CABLE ASSEMBLY				
1		2 PCS		101		325-881-50X		CONNECTOR, MODULAR PLUG, 8 POSITION, 8 CONDUCTOR, 50U" AU, FLAT TYPE EXIT.		REV. 000000		REV. 000000		PART NO. 488-XXB-51X-D		PWS NO. 488-XXB-51X-D				
ITEM		QTY		MFG.		101 PART NO.		DESCRIPTION		DRAWING NO.		REV. 000000		CUSTOMER		DIGI KEY				
								CABLE ASSEMBLY PARTS LIST		SCALE		NONE		SHEET 1 OF 1						



488-258-512-D	250 FT ± 4.0 IN 7.62 M ± 101.6 MM
488-148-512-D	14.0 FT ± 3.0 IN 4.27 M ± 76.2 MM
488-078-512-D	7.0 FT ± 2.0 IN 2.13 M ± 50.8 MM
PART NUMBER I/O INTERCONNECT	LENGTH "X"

11881-25-ND	11881-14-ND	11881-07-ND
-------------	-------------	-------------


CUSTOMER APPROVAL	
ENGR. SIGN <i>Math Lane</i>	
DATE: 4-12-99	

NOTES: UNLESS OTHERWISE SPECIFIED.	
1. CABLE TO BE BUNDLED AND TWIST TIED.	
2. TEST CABLE FOR ALL OPENS & SHORTS.	
3. PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.	

THIRD ANGLE PROJECTION	
UNLESS OTHERWISE NOTED: 1) DIMENSIONS ARE IN INCHES (MILLIMETER) 2) TOLERANCES: XXX ± 0.25 (6.35)	
SCALE: NONE	
SHEET 1 OF 1	

2	"X"	120-810-020	MODULAR CABLE, 26 AWG (7/34) BARE COPPER, 8 CONDUCTOR, UNSHIELDED, WHITE PVC.
1	2 PCS	325-881-50X	CONNECTOR, MODULAR PLUG, 8 POSITION, 8 CONDUCTOR, 50U" AU, FLAT TYPE EXIT.
ITEM	QTY	DOI PART NO.	DESCRIPTION

CABLE ASSEMBLY PARTS LIST			
---------------------------	--	--	--



WIRE DIAGRAM

PI	OPEN END
1	GRAY
2	ORANGE
3	BLACK
4	RED
5	GREEN
6	YELLOW
7	BLUE
8	BROWN

CUSTOMER APPROVAL
ENGR. SIGN Matt Ammer
DATE: 4-13-99

- NOTES: UNLESS OTHERWISE SPECIFIED.
1. TEST CABLE FOR ALL OPENS & SHORTS.
 2. PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

488-148-525-D	121-810-022	14.0 FT (4.3 M)	50.0 IN (1270.0 MM)	WHITE
488-148-524-D	121-810-012	14.0 FT (4.3 M)	50.0 IN (1270.0 MM)	BLACK
488-148-523-D	121-810-002	14.0 FT (4.3 M)	50.0 IN (1270.0 MM)	SILVER SATIN
488-108-522-D	121-810-021	10.0 FT (3.0 M)	42.0 IN (1066.8 MM)	WHITE
488-108-521-D	121-810-011	10.0 FT (3.0 M)	42.0 IN (1066.8 MM)	BLACK
488-108-520-D	121-810-001	10.0 FT (3.0 M)	42.0 IN (1066.8 MM)	SILVER SATIN
488-078-525-D	121-810-020	7.0 FT (2.1 M)	28.0 IN (711.2 MM)	WHITE
488-078-524-D	121-810-010	7.0 FT (2.1 M)	28.0 IN (711.2 MM)	BLACK
488-078-523-D	121-810-000	7.0 FT (2.1 M)	28.0 IN (711.2 MM)	SILVER SATIN
488-058-522-D	121-810-023	5.0 FT (1.5 M)	22.0 IN (558.8 MM)	WHITE
488-058-521-D	121-810-013	5.0 FT (1.5 M)	22.0 IN (558.8 MM)	BLACK
488-058-520-D	121-810-003	5.0 FT (1.5 M)	22.0 IN (558.8 MM)	SILVER SATIN
101 PART NUMBER	101 CABLE PART NUMBER	EXTENDED LENGTH "X"	RETRACTED LENGTH "R"	

TABULATION BLOCK

THIRD ANGLE PROJECTION

UNLESS OTHERWISE NOTED, DIMENSIONS ARE IN INCHES (MILLIMETERS). TOLERANCES: XXX ± 0.25 (6.35)

MODULAR COIL CABLE, 26 AWG (7/34) BARE COPPER, 8 CONDUCTOR, UNSHIELDED, PVC JACKET, (SEE TABULATION BLOCK FOR COLOR).

CONNECTOR, MODULAR PLUG, 8 POSITION, 8 CONDUCTOR, 50u" AU, FLAT TYPE EXIT.

ITEM	QTY	PC	101	MFG.	101 PART NO.	DESCRIPTION
2	1	PC	101		325-881-50X	SEE "TABULATION BLOCK"

CABLE ASSEMBLY PARTS LIST

I/O INTERCONNECT
SANTA ANA, CALIFORNIA

899C COIL CABLE
TO OPEN END, CABLE ASSEMBLY

PART NO. 488-XXB-52X-D
REV. NO. 488-XXB-52X-D
CUSTOMER DIGI KEY
SCALE NONE SHEET 1 OF 1