





## Dimensions: mm (In.)




Without locking ring.




With standard locking ring.



PANEL MOUNTING



SOLDER LUG



POS.1	POS.2	POS.3
ON	OFF	ON
2-3		2-1
1 2 Comm. 3	OPEN	1 2 Comm. 3

## Electrical Specifications:

- Electrical Life: 30,000 make-and-break cycles at full load
- Contact Resistance: 20mΩ max. initial @ 2-4VDC 100mA
- Insulation Resistance: 1,000MΩ min.
- Dielectric Strength: 1,000 V RMS@ sea level.
- Rating: 1A / 250 VAC, 3A / 120 VAC or 28 VDC

## Mechanical Specifications:

- Operating Temperature: -30° C to +85° C

## Materials:

- Case: Diallyl phthalate (DAP)
- Acutuator: Brass, chrome plated.
- Bushing: Brass, nickel plated.
- Housing: Stainless steel.
- Switch Support: Brass, tin plated.
- Terminal/Contact: Brass, silver plated.

Toggle Switch  
108-2MS3T1B1M1QE

**Mountain**  
**Switch**

Available from Mouser Electronics

[www.mouser.com](http://www.mouser.com)

1-800-346-6873

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[108-2MS3T1B1M1QE](#)