

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TE CONNECTIVITY. IT IS NOT TO BE DISCLOSED OR REPRODUCED IN ANY MANNER WITHOUT THE WRITTEN AUTHORIZATION OF TE CONNECTIVITY. ANY VIOLATION OF THIS NOTICE WILL BE PROSECUTED TO THE FULL EXTENT OF THE LAW.

3308-8 (3/11)

LOC
A

DIST
00

THIS DRAWING IS A CONTROLLED DOCUMENT. THIS DRAWING IS A CONTROLLED DOCUMENT. THIS DRAWING IS A CONTROLLED DOCUMENT.

1583007

TE CONNECTIVITY

TE Connectivity

3308-8 (3/11)

8

7

6

5


4

3

2

1

TOOL NUMBER




-1




WIRE SIZE

mm² [AWG]




INSULATION DIAMETER


mm [in.]



INSUL. ADJ.




FLIP LOCATOR




STRIP LENGTH

mm [in.]




CRIMP HEIGHT

mm [in.]




CONTACT PART NUMBERS 

LOOSE PIECE



STRIP FORM



CONTACT DESCRIPTION

APPLIC. SPECIFIC.

91556-1	0.12-0.38 [26-22]	1.10-1.60 [.043-.063]	YES	NO	3.2-3.7 [.126-.146]	0.69-0.78 [.027-.031]	170204-[]	170262-[]	"EI" Series Contacts	114-5035
91556-3	0.50-0.60 [20]	1.25-1.90 [.049-.075]				0.83-0.93 [.033-.037]				
91562-1	0.05-0.08 [28-30]	1.00-1.20 [.039-.047]	NO	YES	3.2-3.7 [.126-.146]	0.60 ± 0.05 [.024 ± .002]	170205-[]	170263-[]	"EI" Series Contacts	114-5035
91562-3	0.13 [26]	1.10-1.30 [.043-.051]				0.66 ± 0.05 [.026 ± .002]				
91566-1	0.14-0.22 [26-24]	1.10-1.60 [.043-.063]	NO	NO	3.2-3.7 [.126-.146]	0.54-0.69 [.021-.027]	170429-[]	170376-[]	"EI" Series Contacts	114-5035
91566-3	0.29-0.52 [22-20]	1.25-1.90 [.049-.075]				0.68-0.83 [.027-.033]				
91570-1	0.05-0.09 [30-28]	1.00-1.20 [.039-.047]	NO	YES	3.2-3.7 [.126-.146]	0.52-0.63 [.020-.025]	170430-[]	170377-[]	"EI" Series Contacts	114-5035
91570-3	0.12-0.15 [26]	1.10-1.30 [.043-.051]				0.58-0.70 [.023-.028]				
91571-1	0.12-0.22 [26-24]	1.10-1.50 [.043-.051]	NO	NO	2.5-3.5 [.098-.138]	0.69-0.83 [.027-.033]	170369-[]	170354-[]	Low Profile "EI" Series Contacts	114-5051
91571-3	0.30-0.35 [22]	1.35-1.90 [.053-.075]				0.69-0.83 [.027-.033]				

1 LIST OF APPLIED CONTACT PART NUMBERS MAY NOT BE COMPLETE AND IS SUBJECT TO CHANGE. FOR CURRENT INFORMATION ON TERMINAL PART NUMBERS, CONTACT THE TOOLING ASSISTANCE CENTER : 1-800-722-1111.

2. AMP, CERTI-CRIMP, and "EI" are trademarks.

3 -1 IS A CERTICRIMP II HAND TOOL ASSEMBLY.
-3 IS A CERTICRIMP II HEAD SUB-ASSEMBLY.

4. THE HAND TOOL INSTRUCTION SHEET, ALSO KNOWN AS AN "IS", FOR MOST CERTI-CRIMP II TOOLS USE IS 408-8547. IF THE TOOL HAS A FLIP LOCATOR USE IS 408-10414.

CERTI-CRIMP II DATA SHEET

DWN: M. YOUNGER 21FEB2012

CHK: B.A.WOLFE 22FEB2012

APVD: B.A. WOLFE 22FEB2012

NAME: CERTI-CRIMP II TOOL DATA SHEET

SCALE: -

SIZE: A1

DRAWING NO: 1583007

SHEET: 1 of 1

REV: C1

TE Connectivity

REVISION RECORD

DATE

DWN

APVD

REVISION RECORD

DATE

DWN

APVD

REVISION RECORD

DATE

DWN

APVD