

[home](#)
[test & measurement](#)
[download](#)

[online catalogue T&M](#)

[clamp-type test probes](#)
[crocodile clips](#)
[test probes](#)
[oscilloscope test probes](#)
[measuring leads](#)
[plugs](#)
[sockets](#)
 [2 mm system](#)
 [2 mm safety system](#)
 [4 mm system](#)
 [4 mm safety system](#)
[sets](#)
[miscellaneous](#)

Search

[company](#)

[corporate association](#)
[location maps](#)
[fairs and exhibitions](#)
[jobs](#)

SEB 2600 G M4

[datasheet for SEB 2600 G M4](#)
[article number: 972354104](#)



[View Full-Size Image](#)



product description:	
description:	Safety built-in socket, 4 mm diameter, touch-protected, M 4 threaded connection and soldering hole, gold-plated brass. For installation into switchpanels and equipment chassis with wall thicknesses up to 6 mm. Accessory BES 1000. Installation hole: 12.2 mm diameter. Tightening torque: 50 Ncm.
typ:	SEB 2600 G M4 gruen/green
system:	4 mm safety system
order number:	972 354-104
color versions:	
technical data	
measurement category	CAT II
norm	IEC 61010
type of contact:	spring unloaded socket
type of termination:	screw / solder
rated voltage:	AC/DC 1000 V
rated current:	32 A
contact resistance:	5 mOhm
mounting:	screw
material	
contact material:	brass
contact surface material:	gold-plated
housing material:	PA
environmental conditions:	
temperature range:	-40°C to +80°C
inflammable class:	
housing:	94 V-2
drawing	

search

Search..

Messetermine

No events