

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14		F1	REV PER ECR 08-002293	25JAN08	JR	TM

AMP WIRE RANGE	UL Listed FILE E13288
12-10 AWG STRANDED	12-10 AWG STRANDED


- 1
- STAMP AMP 12-10* APPROX AS SHOWN

2

3

4

5



50	LOOSE PIECE, BOX	8-31114-2
2500	ON TAPE, REEL 3	31114-3
2500	ON TAPE, REEL 2	31114-2
-	LOOSE PIECE	31114
QTY	PACKAGE TYPE	PART NO.

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 2-8-93	Tyco Electronics Corporation Harrisburg, PA 17105-3608										
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: N/A	DIMENSIONS: MM [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	CHK DA PATTERSON 2-8-93	APVD JL MECKLEY 2-8-93	PRODUCT SPEC -	APPLICATION SPEC -	NAME TERMINAL, RING TONGUE, BUDGET -	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
FOR APPLICATION		TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 2.62-6.64mm² [5,180-13,100] STRANDED			MATERIAL -	FINISH -	WEIGHT -	A2	00779	C-31114	SCALE	10:1	SHEET	1 of 1	REV	F1
TOOLING INFORMATION		1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.														
FOR ORDER ENTRY																	