

HONEYWELL
PART NUMBER
11SX98-T
PRODUCT CODE
VDJ2287

REV	DOCUMENT	CHANGED BY	CHECK
4	0038448	VS 28APR08	BLR

B



B

A

A

A

A



- NOTES
- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF $\varnothing .087$ MAX ON $.188 \pm .002$ CENTERS
 - 2 - TERMINALS ARE PLATED FOR SOLDERING
 - 3 - SWITCH WILL WITHSTAND TEMPERATURE OF 250° F

RELEASE NO. PR-23688
REPLACES

CHARACTERISTICS	
OPERATING FORCE	- - - - 3.5 OZ MAX
RELEASE FORCE	- - - - .75 OZ MIN
DIFFERENTIAL TRAVEL	- - - .001 MAX
OVERTRAVEL	- - - - .004 MIN

ELECTRICAL DATA		
CONTACT ARRANGEMENT SPDT		
28 VOLTS DC RATING		
	SEA LEVEL	50,000 FT
INDUCTIVE	2 AMP	-
RESISTIVE	3 AMP	-

DESIGN UNITS: INCH	
TOLERANCES UNLESS NOTED:	
NO PLACE	X ±
ONE PLACE	.X ±
TWO PLACE	.XX ±
THREE PLACE	.XXX ±
FOUR PLACE	.XXXX ±
ANGLES	±

DRAWN	SPK	12FEB08
CHECK	RJ	12FEB08
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		

Honeywell			
TITLE SWITCH - BASIC			
SIZE	TYPE	DRAWING NAME	REV
B	I	11SX98-T	4

APPROVALS	KEMA, CE	3A 250V ~ T125 5E4	CE
	UL, CSA	3A 250 VAC	UL BRAND L122A

THIRD ANGLE PROJECTION

RASTER

SCALE	-	WEIGHT: .003 LB MAX	SHEET 1 OF 1
-------	---	---------------------	--------------