



MICRO SWITCH
FREEPORT ILLINOIS
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

ACTUATOR-SWITCH

CATALOG LISTING
JS-245

JS-245

M

DRAWING
NUMBER

8

ISSUE

84

REPLACES

RELEASE NO. SR 10880

CHECK

NOV '62

DES

CHECK

NOV '62

DAW

CHECK


NOV 62

LMH

NOV

FO-50378


.09 WIDE X .031 THICK LEVER



CORROSION RESISTANT STEEL ACTUATOR
AND BRACKET (TYPE 302)

.125 APPROX
PRETRAVEL

.455 APPROX
OPERATING
POSITION



DOTTED LINES
INDICATE BASIC
SWITCH IN PLACE

FLEXIBLE INSULATOR

NOTE -



FURNISHED UNASSEMBLED

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS WITH ISMI BASIC SWITCH INSTALLED

OPERATING FORCE-----1 OZ MAX

RELEASE FORCE-----4 GRAM MIN

DIFFERENTIAL TRAVEL-----.030 MAX

OVERTRAVEL-----.030 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
SPECIFIED
DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE (.0) $\pm .030$
TWO PLACE (.00) $\pm .015$
THREE PLACE (.000) $\pm .005$
ANGLES $\pm$

WEIGHT