

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [98268-1057](#)
Status: **Active**
Overview: Premo-Flex™ FFC and Etched Polyimide Jumpers
Description: 1.25mm Pitch Premo-Flex™ FFC Jumper, Same Side Contacts (Type A), 35 Circuits, 0.076m Cable Length, 0.22mm Cable Thickness, Tin(Sn) Plating

Documents:
[Drawing \(PDF\)](#)
[Product Specification PS-98268-001 \(PDF\)](#)
[Packaging Specification PK-98268-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Cable
Series [98268](#)
Comments Contacts on the same side, Type A
Crimp Quality Equipment Yes
Overview Premo-Flex™ FFC and Etched Polyimide Jumpers
Product Name Premo-Flex™ FFC Jumper
UPC 800756941608

Physical
Cable Length 0.076m
Circuits (Loaded) 35
Circuits (maximum) 35
Packaging Type Bag
Pitch - Termination Interface 1.25mm
Temperature Range - Operating -40°C to +105°C
Wire Size AWG N/A
Wire/Cable Type Flat Flex Cable

Electrical
Current - Maximum per Contact 1.4A
Voltage - Maximum 60V AC

Material Info

Reference - Drawing Numbers
Packaging Specification PK-98268-001
Product Specification PS-98268-001
Sales Drawing SD-98268-001



image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[98268Series](#)

Use With
Molex FFC – FPC connector.
Be sure to match like plating

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION