


Home Cubitron II Abrasives

[Products](#) | [Technology](#) | [Resources](#) | [Testimonials](#)

[United States](#) > [Products & Services](#) > [Manufacturing and Industry](#) > [Cubitron II](#) > [Products](#) > [Cable/Wire](#) > **3M™ Round Conductor Flat Cable, 3365 Series, 3365/25, 100 ft.**

3M™ Round Conductor Flat Cable, 3365 Series, 3365/25, 100 ft.

UPC# 00054007307105 3M Product Number 3365/25 3M ID 80610064455

 Print Share

.050" 28 AWG Stranded, PVC, 100 ft.

- 28 AWG wire on .050 inch centers permits mass terminations to a broad line of IDC connectors
- Stranded wire provides flexibility and extended product life
- Zippable for branching or discrete termination
- Available in gray or black
- RoHS compliant

Need Help?

Questions? We can help
[Contact Us](#)

www.facebook.com
is not loading.

[Overview](#) [Support](#)

Specifications

Color Gray Standard or Black (See Ordering Information)

Shape Flat

People who viewed this item also viewed



3M™ 4-Wall Header .100 in.,
High Temp Option, Straight,
30 Contacts, 3440-6302



3M™ Round Conductor Flat
Cable, 3801 Series,
C3801/14, 100 ft.



3M™ High Flex Life Cable,
3319 Series, 3319/14, 100 ft.



3M™ Wiremount Plug, 4600
Series, 4620-6000



3M™ Round Conductor Flat
Cable, 3801 Series, 3801/40,
100 ft.