










注；

1. 適用電線範囲 : AWG #28~26
(UL1571, UL1061)
被覆外径 : 0.83~10.5
(但し、使用電線について適合性)
2. 材料 : ハウジング : ガラス入り
コンタクト : 錫めつき銅
3. 適用製品規格番号 : 108-5217
4. 取付適用規格番号 : 114-5103

NOTES;



1. APPLICABLE WIRE SIZE : AWG #28~26
(UL1571,UL1061)
INSULATION DIA RANGE : 0.83~1.05
2. MATERIAL :
HOUSING : P.B.T. (G.F)UL94V-0
CONTACT : PRE-TIN PHOS BRONZE
3. PRODUCT SPEC : 108-5217
4. APPLICATION SPEC : 114-5103

3-173985-5	15	28	32
3- ↑ -4	14	26	30
3- -3	13	24	28
3- -2	12	22	26
3- -1	11	20	24
3- -0	10	18	22
2- -9	9	16	20
2- -8	8	14	18
2- -7	7	12	16
2- -6	6	10	14
2- -5	5	8	12
2- -4	4	6	10
2- -3	3	AS SHOWN 図示	
2-173985-2	2	AS SHOWN 図示	
LIGHT BLUE ライトブルー	Pos. 極数	G	H
PART No. 製品番号			



RECOMMENDABLE P.C. BOARD LAYOUT
推奨基板寸法
(適用基板厚0.8~1.6)
(P.C.B THK:0.8~1.6)

F1	REVISED PER ECO-11-005033	RK	HMR	2APR1
LTR	RE (REVISION RECORD)	DR	CHK	DATE

		 TE Connectivity	
組合電線断面積 (WIRE RANGE) NOTE 1 mm ² (AWG -)	被覆外径 (INSULATION DIA.) NOTE 1 mmφ	名称 (NAME) CT AMP-IN HEADER 2mm PITCH MT VERTICAL (V-TYPE)	
材料 (MATERIAL) NOTE 2	仕上 (FINISH) 	一般公差 (GENERAL TOLERANCE) 10以下: ±0.2 10以上 30以下: ±0.25 30以上 100以下: ±0.3 100以上: ±3%	LOC B J
DR. 23/AUG/'99 J. TSUJI	DE. 23/AUG/'99 	番号 (No.) C-173985	尺度 (SCALE) 5-1
CHK. 23/AUG/'99 	APP. 	REV. F1	SHEET 1 OF 1

(CUSTOMER DRAWING) 参 考 图 面