

12V Drill / Screwdrivers - Cordless



Model Number	DC727KA	DC740KA	DC756KA	DC940KB
No Load Speed	0-450/0-1400 rpm	0-350/0-1200 rpm	0-400/0-1400 rpm	0-450/0-1450/0-1800 rpm
Drilling Capacity Steel	10 mm	10 mm	13 mm	13 mm
Drilling Capacity Wood	25 mm	25 mm	28 mm	38 mm
Maximum Torque	32 N-m	20 N-m	35 N-m	48 N-m
Battery	2 x 1.3Ah Ni Cd	2 x 1.3 Ah Ni-Cd	2 x 2.0 Ah Ni Cd	2 x 2.6Ah Ni MH
Weight	1.7 kg	1.6 kg	2.0 kg	2.3 kg

DC727KA



12V mid handle drill/driver. Two speed settings, variable speed and reverse switch for control-able use. 17 position adjustable torque control. Supplied with charger, 2 x 1.3Ah Ni Cd battery packs and carrying case.

Description	Order Code	Price Each
DC727KA drill/screwdriver	135-2954	
Replacement battery DE9074	135-2977	

DC740KA



12V cordless drill/screwdriver. Two speed settings, variable speed and reverse switch for maximum control. 10mm single sleeve chuck and spindle lock for easy bit change. Supplied with charger, 2 x 1.3Ah Ni Cd battery packs and carrying case.

Description	Order Code	Price Each
DC740KA drill/screwdriver	135-2958	
Replacement battery DE9074	135-2977	

DC756KA



12V drill driver for drilling and screwdriving applications. Two speed settings, variable speed and reverse action. 17 position adjustable torque control. 13mm single sleeve keyless chuck. Supplied with charger, 2 x 2.0Ah Ni Cd battery packs and carry case.

Description	Order Code	Price Each
DC756KA drill/screwdriver	135-2960	
Replacement battery DE9091	135-2979	

DC940KB



12V drill/driver suitable for drilling and screw-driving applications. Three speed settings for optimum performance in high torque, normal use and high speed applications. Twenty two position adjustable torque control settings for precise screwdriving. 13mm keyless chuck with automatic spindle lock. Supplied with one hour charger, 2 x 2.6Ah Ni MH battery packs and heavy duty carry case.

Description	Order Code	Price Each
DC940KB drill/screwdriver	135-2967	
Replacement battery DE9501	135-2987	