

Current refinements (click ☐ to remove) Search Tips

☒ Region ☒ USA ☒ Product Family ☒ HSTT Heat Shrink Bulk Reels ☒ Text Search: 'HSTT50-T'

Your search criteria matched only one product, shown below.



Flexible Polyolefin DRYSHRINK™Heat Shrink Tubing

- General Purpose heat shrink tubing for dry locations
- Applications include insulating, protecting, harnessing and identifying wires.
- Material Type: Crosslinked Polyolefin
- Shrink Ratio: 2:1
- Temperature Range:-67°F to 275°F (55°C to 135°C)
- Flammability Rating: Flame retardant EXCEPT clear
- Voltage: 600 V
- UL Recognized, CSA Certified
- Mil Spec: AMSDTL-23053/5 Class 1 (Colors) Class 2 (Clear)

Part Number:	HSTT50T
RoHS Compliancy Status:	Compliant
Part Description:	Thin Wall Polyolefin Heat Shrink
Material:	Polyolefin cross-linked
Color:	Black
CSA Certified:	Yes
Military Specification:	AMS-DTL-23053/5 Class 1
UL Recognized:	E122770
Flammability Rating:	Flame Retardant
Length Per Reel (ft.):	200
Length Per Reel (m):	61.1
Max. Recovered I.D. (In.):	.250
Max. Recovered I.D. (mm):	6.4
Min. Expanded I.D. (In.):	.500
Min. Expanded I.D. (mm):	12.7
Nominal Diameter / Size:	.500
Nominal Recovered Wall Thickness (In.):	.025
Nominal Recovered Wall Thickness (mm):	.6
Shrink Ratio:	2:1
Temperature Range:	-67°F to 275°F (55°C to 135°C)
Min. Order UOM:	RL
Min. Order Qty.:	1
BOM Qty. (# of Pkgs.)	0

Add to My Catalog

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.