


Single Digit Displays

Shape	Part Number	Emitting Color	Emitting Material	Wave Length (nm)	Luminous Intensity IF=10mA (ucd) Min. Max.	Common	Figure No.
0.52"(13.2mm)	DHR13A / DHR13C	Red	GaP	700	900 - 2200	Anode / Cathode	7
	DUR13A / DUR13C	Red	GaAsP/GaP	625	2200 - 5600	Anode / Cathode	
	DMR13A / DMR13C	Red	GaAlAs	660	5600 - 21000	Anode / Cathode	
	DUG13A / DUG13C	Green	GaP	565	5600 - 17000	Anode / Cathode	
	DUY13A / DUY13C	Yellow	GaAsP/GaP	590	2200 - 5600	Anode / Cathode	
0.56"(14.2mm)	DHR14A / DHR14C	Red	GaP	700	560 - 1400	Anode / Cathode	8
	DHR14A-1 / DHR14C-1						
	DUR14A / DUR14C						
	DUR14A-1 / DUR14C-1	Red	GaAsP/GaP	625	2200 - 5600	Anode / Cathode	
	DMR14A / DMR14C						
	DMR14A-1 / DMR14C-1	Red	GaAlAs	660	5600 - 21000	Anode / Cathode	
	DUG14A / DUG14C						
	DUG14A-1 / DUG14C-1	Green	GaP	565	5600 - 14000	Anode / Cathode	
	DUY14A / DUY14C						
DUY14A-1 / DUY14C-1	Yellow	GaAsP/GaP	590	2200 - 5600	Anode / Cathode		

7



8

