

## ToLEDo BENT TIP 3W S E14 SL

0126295

### Range features



### PRODUCT OVERVIEW

Ordering number	0126295
Technology	LED
Light colour	827 Homelight
Energy class	A++
Average life (Rated) (h)	15000
Lamp shape	Candle Bent-tip
Lamp finish	frosted
Dimmable	No
Cap/Base	E14
Type	ToLEDo Bent Tip Candle
EAN code	5410288262956
CRI (Ra)	80
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	250
Efficacy (Rated) (lm/w)	83
Watt (Nominal) (W)	3
Equivalent watt (W)	25
Voltage (V)	220-240

# ToLEDo BENT TIP 3W S E14 SL

0126295

## DATA TABLE

### General data

<b>Dry applications use only</b>	Yes
<b>Ordering number</b>	0126295
<b>Technology</b>	LED
<b>Energy saving lamp</b>	Yes
<b>Average life (Nominal) (h)</b>	15000
<b>Average life (Rated) (h)</b>	15000
<b>Energy class</b>	A++
<b>Lamp finish</b>	frosted
<b>Lamp shape</b>	Candle Bent-tip
<b>Dimmable</b>	No
<b>Cap/Base</b>	E14
<b>Type</b>	ToLEDo Bent Tip Candle
<b>EAN code</b>	5410288262956
<b>Long description</b>	
<b>Product name</b>	ToLEDo BENT TIP 3W S E14 SL
<b>Lamp mercury content (mg)</b>	0
<b>Starting time (max) (s)</b>	0.05
<b>Warm-up time to 60% of full light (max) (s)</b>	< 1s => 60%
<b>Control gear required</b>	No
<b>Fixture rating</b>	Open
<b>Intended purpose</b>	General lighting
<b>No. of switching cycles before premature failure (min)</b>	>7500
<b>Special purpose lamp</b>	No
<b>Transformer required</b>	No
<b>Sales pack quantity</b>	1
<b>Optimal operating condition (°C)</b>	25

### Optical data

<b>Light colour</b>	827 Homelight
<b>CRI (Ra)</b>	80
<b>Suitable for accent lighting</b>	No
<b>Colour temperature (K)</b>	2700
<b>Luminous flux (Rated) (lm)</b>	250
<b>Luminous flux (Nominal) (lm)</b>	250
<b>Lumen maintenance at end of nominal life (%)</b>	70
<b>Chromaticity coordinate Y</b>	-1
<b>Chromaticity coordinate X</b>	-1
<b>Adjustable chromaticity</b>	No

## ToLED<sub>o</sub> BENT TIP 3W S E14 SL

0126295

### Electrical data

<b>kWh per 1000 hours burning time</b>	3
<b>Efficacy (Rated) (lm/w)</b>	83
<b>Watt (Rated) (W)</b>	3
<b>Watt (Nominal) (W)</b>	3
<b>Equivalent watt (W)</b>	25
<b>Voltage (V)</b>	220-240
<b>Lamp power factor</b>	0.35


### Physical data

<b>Weight (kg)</b>	0.05
<b>Lamp Length (mm) - C/L</b>	130
<b>Max. Lamp Diameter (mm) - D</b>	37
<b>Lamp dimension equal to filament lamp equivalent</b>	Yes
<b>Single packaging type</b>	Box/Sleeve
<b>Single package dimensions (L x W x H) (cm)</b>	5.50 x 5.50 x 14.00
<b>Inner package dimensions (L x W x H) (cm)</b>	29.00 x 12.00 x 16.00
<b>Inner package net weight (kg)</b>	0.47
<b>Outer package dimensions (L x W x H) (cm)</b>	62.50 x 30.50 x 34.50

ToLED<sub>o</sub> BENT TIP 3W S E14 SL

0126295

## TECHNICAL DRAWINGS



## ENERGY LABEL

