




PC card drilling dimensions(after plating)
(thickness 2.40±0.20mm)



Notes:

1) The nut can protrude above the surface of insulator but maintaining the footprint dimension 6±0.15 mm.

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0000

LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER		
09	30.81	24.99	16.96	16.79	10.96	D09P24B4P*00LF	D09P24B5P*00LF	D09P24B6P*00LF
15	39.14	33.32	25.18	25.12	19.18	D15P24B4P*00LF	D15P24B5P*00LF	D15P24B6P*00LF
25	53.03	47.04	39.12	38.84	33.12	D25P24B4P*00LF	D25P24B5P*00LF	D25P24B6P*00LF
37	69.32	63.50	55.68	55.30	49.68	D37P24B4P*00LF	D37P24B5P*00LF	D37P24B6P*00LF
						Gold flash	0.40 µ gold	0.76 µ gold

Threaded ØT M3 = L
Threaded ØT 4.40 = X

mat'l. code				surface	ISO 1302	tolerance	ISO 406	ISO 1101	projection	product family
-				ISO 1302	✓	ISO 406	ISO 1101	ISO 1101	MM	D-SUB
ltr	ecn no	dr	date	angles	linear	.0±0.1	.00±0.1	.000±0.1	scale 2:1	title
G	ELX-I-21256	AB	2015/07/14	0°±2'						MALE CONNECTOR DELTA-D
										STRAIGHT - SOLDER TYPE FOR PCB 2.4mm
				dr	LELEON	1992/09/14				
				engr	ALIAS BABU	2015/07/14				
				chr	MITHUN PAUL	2015/07/14				
				app	BIJU K PAUL	2015/07/14				
sheet index	revision	G								dwg no
	sheet	1								sheet 1 of 1
										size
										A3
										type
										Product Customer Drawing