


SPECIFICATION FOR APPROVAL

TO: 頂興


2/1

PART NAME	EMI FILTER	YUNPEN SAMPLE NO	YUD-0535
YUNPEN MODEL	YB01A1	SAMPLE DATE	APR-28-2004
MODEL NO		OUR DRAWING NO	

1. PHYSICAL DIMENSIONS:(mm)



2. SCHEMATIC:



CX : 0.1uF
CY : 3300pF
L : 2x3.7mH

REPORTED BY	CHECKED BY	APPROVED BY	3	
凡灵楚 4/28 17:05	区21011 5/06/04 8:00	4/29 17:15	2	
			REV. 1	

SPECIFICATION FOR APPROVAL

TO: 頂興

2/2

PART NAME	EMI FILTER	YUNPEN SAMPLE NO	YUD-0535
YUNPEN MODEL	YB01A1	SAMPLE DATE	APR-28-2004
MODEL NO		OUR DRAWING NO	

3.ELECTRICAL CHARACTERISTICS:

- 3-1.RATED VOLTAGE 125/250VAC
 3-2.RATED CURRENT1A
 3-3.OPERATING FREQUENCY 50/60Hz
 3-4.LEAK CURRENT:EACH LINE TO GROUND
 250VAC 50Hz 0.8mA MAX
 3-5.HIPOT RATING.(FOR ONE MINUTE)
 LINE TO LINE 1450VDC
 LINE TO GROUND 1800VAC
 3-6.INSULATION RESISTANCE 250VDC/100MOHM MIN
 3-7.DIRECT CURRENT RESISTANCE 0.5 OHM MAX
 3-8.OPERATING TEMPERATURE -25 TO +85 °C

4.SAFETY COMPLIANCE:

UL FILE NO:E134751
 CSA FILE NO:LR95210
 VDE FILE NO:40007880
 SEMKO FILE NO:9444068
 FIMKO FILE NO:184116-01...03
 NEMKO FILE NO:P95102844
 DEMKO FILE NO:303953

REPORTED BY	CHECKED BY	APPROVED BY	3	
凡灵芝 4/28 22:05	DR POWELL 4/28 17:00	4/28 17:45	2	
			REV. 1	