

Rating	10A 125V, 6A 250V AC 1/2HP 125/250VAC	
	20A 14VDC	
Contact Resistance	50m ohm Max.	
Insulation Resistance	DC 500V 100M ohm Min.	
Dielectric Strength	AC 1500V 1 minute	
Operation Temp.	- 25 ° C ~ 85 ° C	
Function	4P DPST (ON)-OFF	

()=Momentary Function

MATERIAL:

Frame: Black, Nylon 66 (94-V2)


Actuator: PC Clear (94-V2), For Color
Ref. "X" in Actuator Color Chart
and CW P/N.

Terminals: Silver plated, Copper alloy

Waterproof Rubber: Black, Silicone


Printed: None

Waterproof: IP65



Full travel: 4.5mm

ACTUATOR COLOR	X
Amber	A
Black	B
Green	G
Red	R
Blue	U
White	W



RoHS Compliant

CW INDUSTRIES
Southampton, Pa. 18966
Tel 215.355.7080/www.cwind.com

Date Drawn: 6-07-12

Rev. 0

Unit: mm

Checked By: *G. Gold*

Title:
PUSH BUTTON SWITCH

CW P/N:
GPB527A202BX