




CB4200 Series Single Pole




Internal Wiring Diagram



CB4200 Series Double Pole



Internal Wiring Diagram



Technical Data

Rated voltage & current†

UL

CSA

VDE

Creepage resistance

Dielectric strength

Insulation resistance

Interrupting capacity
(VDE 0660, Part 101, P-2)Interrupting capacity; 4201
(UL 1077/EN 60934 PC1)

Typical life at 2 x rated current

Shock

Torque

Vibration

Temperature range

Corrosion

Humidity

Weight

Wire size (UL)

Voltage Ratings

Current Ratings

AC 250 V, DC 65 V, 50/60 Hz 0.05...16 A

AC 250 V, DC 65 V, 50/60 Hz 0.05...16 A

AC 250 V, DC 65 V, 50/60 Hz 0.05...16 A

PTI 600 to IEC 112

4,000 VAC; IEC 664 & 664 A

> 100 MM (DC 500 V)

4201-10 Maximum capacity

0.05...0.8 A Self-limiting

1...2 A 200 A

2.5...16 A 400 A

Rated current Rated voltage Maximum capacity

0.05...2.0 A AC 250 V 200 A

2.0...16 A AC 250 V 200 A

20 A AC 125 V 400 A

5,000 operations

25 g (11 ms) to IEC 68-2-27, Test Ea

1.2 Nm

5 g (57 to 500 Hz / ±0.38 mm, 10 to 57 Hz) to IEC 68-2-6, Test Fc

-30°C...+55°C (-22°F...+131°F)

96 hours at 5% salt spray, to IEC 68-2-11, Test Ka

240 hours at 95% RH, to IEC 68-2-3, Test Ca

60 g per pole

#20...8 AWG solid/0.5...6 mm²

Accessories

Jumpers

Daisy Chain 50*

Straight CQB**

insulated

Angled CQB**

insulated

Adapter foot (for TS 32 Rail)

Busbar

Single pole 1 meter

Busbar end cap for 6720000227

Power lug for 6720000227

Marking Tags

Note: Part numbers are shown
for a single card of pre-printed
tags numbered 1-50.

Special print only

Consecutive horizontal

Consecutive vertical

Type	Part No.
BDC 50	9970290000
CQB 2	9970560000
CQB 3	9970570000
CQB 4	9970580000
CQB 10	9970590000
CQB 2	9970600000
CQB 3	9970610000
CQB 4	9970620000
CQB 10	9970630000
MCBAF/TS 32	9102100000
	6720000227
	6720000225
	6720000226

WS 8/5 MC	1640750000***
DEK 5/5	0473460001
DEK 5/5	0473560001

†Note: Resistive and inductive loads (0.05 - 16 A)

*BDC will accommodate 20 A per pin, 20 A total

**CQB will accommodate 18 A per pin, 18 A total; dedicated to 4201 Series

***Please specify horizontal or vertical print when ordering.

Standard quantity = 144 tags per card.