



SMB/SMC Series

ELBOW BULKHEAD JACKS AND SOCKETS/50 OHM (for flexible cable)

Solder spill socket (male center contact)




mounting detail




Body Plating	Contact Plating	Part Number	
		SMB	SMC
Gold	Gold	B65 M09 G999 X99	C65 M09 G999 X99
Bright Nickel	Gold	B65 M09 J999 X99	C65 M09 J999 X99

STRAIGHT BULKHEAD JACKS/50 OHM

Solder center contact clamp outer (male center contact)



mounting detail



Cable Group ①	Body Plating	Contact Plating	Part Number	
			SMB	SMC
022	Gold	Gold	B65 H05 G022 X99	C65 H05 G022 X99
022	Bright Nickel	Gold	B65 H05 J022 X99	C65 H05 J022 X99
024	Gold	Gold	B65 H05 G024 X99	C65 H05 G024 X99
024	Bright Nickel	Gold	B65 H05 J024 X99	C65 H05 J024 X99

① For cable group to cable type cross reference refer to page 200.

All diagrams are for SMB versions.

All dimensions are nominal.

For 75 ohm versions see page 157 to 167, or contact our sales office for uncataloged requirements.

All measurements are in millimeters unless otherwise specified.

M/A-COM, Inc.

North America: Tel. (800) 366-2266
Fax (800) 618-8883

Asia/Pacific: Tel. +85 2 2111 8088
Fax +85 2 2111 8087

Europe: Tel. +44 (1344) 869 595
Fax +44 (1344) 300 020