

Data Sheet

Whether you are testing for OSHA compliance, quieting equipment, or monitoring the roar of a stadium crowd, B+K Precision's Sound Level Meters can get the job done. The model 732A and 735 Sound Level Meters provides 30~130 dB capability in three convenient measurement ranges Low, Med and Hi with an accuracy of ± 1.5 dB. The meter meets the IEC 651 Type II and includes frequency weighting A & C and fast and slow time weighting. Two auxiliary ports provide either AC output, 1Vrms full scale, or DC output, 10mV/dB. With models 732A or 735, B&K Precision can meet all your sound testing needs.

Models 732A & 735 Sound Level Meters

Common features

- RS-232 Interface
- Bargraph
- MAX/MIN function
- Auto Ranging (30 ~ 130dB)
- Resolution 0.1dB
- Level Range Display
- AC/DC Signal Output
- Auto Power Off
- Backlit LCD

Model 735 only

- Windows Software Included
- Clock Display
- 32,000 Records Data Logger



Back Light Function

RS-232 Interface

RS-232 Software
for Windows 95/98/
2K/XP included with
model 735



Model 732A

The CAL73 sound level calibrator is used to calibrate sound level meters and other sound measurement equipment. You can calibrate 1 inch diameter microphones directly and 1/2 inch microphones using 1/2 inch adapter supplied with the calibrator.

Model CAL73 Sound Level Calibrator

- Conforms to IEC 60942 (2003) Class 2, ANSI S1.40-1984
- 94dB and 114dB Sound calibrator at 1KHz
- Accurate and simple to use
- Fits 1 inch and 1/2 inch microphones



Model CAL73

B&K Precision Corporation

22820 Savi Ranch Parkway, Yorba Linda, CA 92887
Tel: 714-921-9095, Fax: 714-921-6422
www.bkprecision.com

Specifications subject to change without notice