




REV. 0

DCO 141524


COIL: @ 25°C
 RESISTANCE 1560 OHMS $\pm 10\%$
 NOMINAL VOLTAGE 26.5 VDC
 MUST OPERATE 14.2 VDC
 MUST RELEASE 8.0 VDC MAX, 1.37 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's
 SHOCK 75 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2 MS MAX
 RELEASE TIME 1.5 MS MAX
 CONTACT BOUNCE 1.5 MS MAX

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO
 1A 28 VDC RESISTIVE 100,000
 OPERATIONS

DR. B.D. 11/16/99

CK JERRY C 11/16/99

COMMUNICATIONS
 INSTRUMENTS, INC.

CUST. C.I.I.
 CUST. NO. STANDARD REV.

"PRMA" RELAY

PRMAC-26XS