


**Part Number: 87061-0001**

2.50mm / 3.50mm Pitch Low Profile Female Crimp Terminal, Tin (Sn) Overall



Series image - Reference only

**Status:** **OBSOLETE**  
**Replacement:** Contact Molex  
**Series:** [87061](#)  
**Category:** Crimp Terminals

**Use With:**[5264](#) housings**Product Environmental Compliance**[EU RoHS:](#) ELV and RoHS Compliant[China RoHS:](#) [REACH SVHC:](#) Not Reviewed[Low-Halogen Status:](#) Not Reviewed**Part Detail****General**

<b>Status</b>	<b>Obsolete</b>
Category	Crimp Terminals
Series	<a href="#">87061</a>
Application	Signal
Product Name	N/A

**Physical**

Durability (mating cycles max)	30
Gender	Receptacle
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Packaging Type	Reel
Wire Insulation Diameter	1.90mm max.
Wire Size AWG	22, 24, 26, 28
Wire Size mm <sup>2</sup>	DIA.1.15-1.9

**Electrical****(Please review the Product Specification for specific details.)**

Current - Maximum per Contact	3A
Voltage - Maximum	250V AC (RMS)/DC

**Material Info****Reference - Drawing Numbers**

Sales Drawing	SD-87061-0001
---------------	---------------

**Application Tooling**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

**Crimp Quality Equipment**

[Molex also offers wire strippers, pull testers, shut-height gauges, micro-meters and more](#)

**Previously Available Application Tooling**

[Check our list of old tooling that used to be available for this part](#)