



LOC	DIST	REVISIONS					
		#	LYR	DESCRIPTION	DATE	DWN	APVD
AD	14	A		REVISED PER 0430-0163-97	5/15/97	RB	MB
		B		REVISED PER 0430-0204-97	6/3/97	RB	MB
		C		REVISED PER 0430-0286-97	8/14/97	RB	MB
		D		REVISED PER 0G51-0101-98	7/15/98	RB	DD
		E		REVISED PER 0G51-0107-98	8/4/98	RB	DD
		F		REV PER EC 0G51-0226-98	01/17/99	MM	EL
		G		REV PER EC 0G51-0294-98	01/20/99	MM	DD
		H		REV PER 0G51-0062-99	05/17/99	MM	EL
		H1		REV PER ECO-09-021826	07JAN10	KK	AEG



- ⚠ MATERIAL: HOUSING, THERMOPLASTIC, COLOR: BROWN.
CONTACTS, PHOSPHOR BRONZE.
HOLD-DOWNS, BRASS.
- ⚠ FINISH: CONTACTS, 1.27 MIN. MICROMETERS NICKEL ALL OVER,
0.38 MIN. MICROMETERS GOLD OVER NICKEL IN CONTACT AREA,
- ⚠ FINISH: 2.54 MIN MICROMETERS TIN-LEAD OVER NICKEL ON SOLDER TAILS.
- ⚠ FINISH: CONTACTS, 1.27 MIN. MICROMETERS NICKEL ALL OVER,
0.0254-0.0762 MICROMETERS GOLD OVER NICKEL IN CONTACT AREA.
2.54 MIN. MICROMETERS TIN-LEAD OVER NICKEL ON SOLDER TAILS.
- ⚠ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE	⚠ 4	⚠ 3	3.18	145251-6
	⚠ 4	⚠ 3	2.54	145251-5
⚠ OBSOLETE	⚠ 2	⚠ 3	3.18	145251-3
	⚠ 2	⚠ 3	2.54	145251-2
⚠ OBSOLETE	⚠ 2	⚠ 3	2.16	145251-1
PLATING		W	PART NO	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R BROWN	1/6/97	AMP AMP Incorporated Harrisburg, PA 17105-3608	
		CHK M BOWERS	1/6/97		
		APVD D SARVER	1/6/97		
		PRODUCT SPEC			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME AMP, 1mm ⌀ STANDARD EDGE ASSEMBLY, 242 POSITION	
mm		0 PLC ±-			
		1 PLC ±-			
		2 PLC ±0.13			
		3 PLC ±-			
		4 PLC ±-			
		ANGLES			
		FINISH			
MATERIAL		WEIGHT		SIZE A1 00779	
		CUSTOMER DRAWING			
		DRAWING NO		C-145251	
		SCALE			
		SHEET		1 OF 2	
		REV			
		H1			

