

Toggle Clamp - Vertical



- The most popular of toggle clamps
 - High clamping forces can be generated
 - Complete with cushioned PVC handle grip
 - Extendible base to guide the clamping arm
 - Removable stop pin to alter operating angles
 - Zinc-plated and passivated steel
- | | V75/2B | V150/2B | V250/2B | V350/2B |
|--|----------|-----------|----------|----------|
| Nominal holding force | 75kg | 150kg | 250kg | 350kg |
| Weight | 0.05kg | 0.15kg | 0.38kg | 0.8kg |
| Height | 98 | 125 | 175 | 220 |
| Length | 57 | 70 | 110 | 146 |
| Hole centres | 24 x 16 | 27 x 12.7 | 32 x 19 | 45 x 32 |
| Hole  | 4.4 | 5.1 | 7.1 | 8.3 |
| Clamp arm length | 31 | 43 | 74 | 95 |
| Order Code | 714-7510 | 714-7521 | 714-7533 | 714-7545 |

MAT113/225430,401808

Mfrs. List No.	Order Code	Price Each
V75/2B	714-7510	
V150/2B	714-7521	
V250/2B	714-7533	
V350/2B	714-7545	