

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [19203-0159](#)
Status: **Active**
Overview: [High-Temperature Temp Terms Terminals and Splices](#)
Description: Krimptite™ Temp-Term Ring Tongue Terminal for 10 to 12 AWG Wire, Stud Size 6 (M3.5)

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-19902-011 \(PDF\)](#)
[Product Specification PS-19902-013 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E32244

General

Product Family Ring and Spade Terminals
Series [19203](#)
Comments 1200° F (649° C)
Crimp Quality Equipment Yes
Mil-Spec N/A
Overview [High-Temperature Temp Terms Terminals and Splices](#)
Product Name Krimptite™, Temp-Terms
Type Ring
UPC 800755059755

Physical

Barrel Type Closed
Insulation None
Material - Plating Mating Tin
Net Weight 1.444/g
Packaging Type Bag
Stud Size 6 (M3.5)
Wire Size AWG 10, 12
Wire Size mm² 4.00 - 6.00

Material Info

Old Part Number C-U-128-06

Reference - Drawing Numbers

Product Specification PS-19902-011, PS-19902-013
Sales Drawing CCD10104



image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?
Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[19203Series](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.
Global

Description	Product #
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640070100
PremiumGrade™ Hand Crimp Tool	0640030100

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19203-0159](#)