



# Sta-Kon®

**T&B Catalog Number:****10RC-10FLX****UPC Number:**


78621080727

**Description:**

Expanded Insulated Vinyl Locking Fork Terminal For Wire Range 12-10 Stud Size #10, Yellow

**Status:**

Active

**WEB USE**

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>**Features**

Locking fork terminals have a specially designed tongue that lets them go on like a fork and stay on like a ring.

**General**

Insulation Type Expanded Insulated Vinyl

Terminal Series RC

Material Copper

Finish Electro -Tin Plated

Color Yellow

Wire Range 12-10

Stud Size #10

**Dimension Information**

Maximum Insulation (inches) .250

Stock Thickness .04

A (inches) 1.10

B (inches) .37

C (inches) .27

M (inches) .91

**Specifications**

Temperature Rating 105°C

Flammability Rating UL 94 V-0

**Tooling**

Tool Charts Available on Website

Application Tools ERG2001, ERG2003, WT145C, WT2000, WT112M, WT145C

**Packaging**

T&amp;B Order Multiple 50

T&amp;B Inner Pack 50

Package in Units 500

Package Type Standard

T&amp;B Sold in UOM Each

T&amp;B Weight Per UOM 0.54 lbs. per 100

Alternate Package Qty RC2227-250

**Application Support**

Overview Available on Website

Wire Guide Tables Available on Website

**Certifications**

RoHS Compliance Yes

### Certifications



File Nbr:

E9809

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:[techsupport@tnb.com](mailto:techsupport@tnb.com)