


4

3


2

1


UNIT: mm



PIN ASSIGNMENT:



Electrical test:
1. 100% short, open, miswire test
2. Conduct resistance: 2.0Ω (max)
3. Insulation resistance: $5M\Omega$ (min)
4. dielectric test: DC 300V




1PC/PE BAG

⑥	PE BAG	1/10	CLEAR SIZE: 280*330*0.05mm PRINT BLACK*MADE IN CHINA*+10PCS"
⑤	PE BAG	1	CLEAR SIZE: 130*230*0.05mm PRINT BLACK*MADE IN CHINA*+1PC"
④	TIE	2	WHITE L=100mm
③	OUT JACKET	6g	BEIGE(V-29#) PVC-40P (MOULD NO:WM-40)
②	CABLE	1	BEIGE(V-29#) USB2.0 UL2725 28#/1P+24#/2C+AEB OD:4.7mm L=2000±10
①	CONN	1	USB A MALE NICKEL PIN G/F 3PCS TYPE
NO.	NAME	Q'TY	SPECIFICATION

CnC Tech, LLC
Industrial Cable and Connector Technology

DRAWN	ZHONGHS	DRAWING NO	
CHECKED		CUSTOMER	CNC
APPROVAL		ITEM NO.	102-1023-BE-00200
DECIDED		DATE	2012-05-16
VERSIONS/EDITION	A/0	PROJECTION	

NOTE:
1. 小PE袋/大PE袋对应料号. 包装袋数量及时间印刷样式:



2. 外箱两个侧唛ITEM NO后面各贴一个35*22mm ROHS标签。