

High Security Industrial Padlocks
Xenoy Covered Laminated Steel



- High security laminated steel for superior strength
- Xenoy thermoplastic cover withstands attacks and extreme temperatures
- Hardened boron alloy shackle for superior cut resistance
- High security 6 spool pin cylinder for maximum pick resistance
- Double ball bearing locking protects against prying and hammering
- Estane shackle seal keeps water out (open shackle versions)
- Removable cylinder can be replaced or repinned
- Supplied with 2 keys

Shackle Type	Size (mm)	Shackle $\varnothing$	Vertical Clearance	Horizontal Clearance
Open	54	8	29	22
Open	67	11	35	22
Long	54	8	63	22
Closed	54	8	20	23
Closed	67	11	20	23

418278.425783

Size (mm)	Order Code	Price Each
Open Shackle Padlocks		
54	105-7989	
67	105-7990	
Long Shackle Padlocks		
54	105-7991	
Closed Shackle Padlocks		
54	105-7992	
67	105-7993	