


High Voltage MLC Radials (SV Style)



Application Information on High Voltage MLC Capacitors



High value, low leakage and small size are difficult parameters to obtain in capacitors for high voltage systems. AVX special high voltage MLC radial leaded capacitors meet these performance characteristics. The added advantage of these capacitors lies in special internal design minimizing the electric field stresses within the MLC. These special design criteria result in significant reduction of partial discharge activity within the dielectric and having, therefore, a major impact on long-term reliability of the product. The SV high voltage radial capacitors are conformally coated with high insulation resistance, high dielectric strength epoxy eliminating the possibility of arc flashover.

The SV high voltage radial MLC designs exhibit low ESRs at high frequency. The same criteria governing the high voltage design carries the added benefits of extremely low ESR in relatively low capacitance and small packages. These capacitors are designed and are ideally suited for applications such as snubbers in high frequency power converters, resonators in SMPS, and high voltage coupling/DC blocking.

COG Dielectric General Specifications

Capacitance Range

10 pF to 0.15 μ F
(+25°C, 1.0 $\pm$ 0.2 Vrms at 1kHz,
for $\leq$ 100 pF use 1 MHz)

Capacitance Tolerances

$\pm$ 5%; $\pm$ 10%; $\pm$ 20%

Operating Temperature Range

-55°C to +125°C

Temperature Characteristic

0 $\pm$ 30 ppm/°C

Voltage Ratings

600 VDC thru 5000 VDC (+125°C)

Dissipation Factor

0.15% max.
(+25°C, 1.0 $\pm$ 0.2 Vrms at 1kHz,
for $\leq$ 100 pF use 1 MHz)

Insulation Resistance (+25°C, at 500V)

100K M Ω min. or 1000 M Ω - μ F min.,
whichever is less

Insulation Resistance (+125°C, at 500V)

10K M Ω min., or 100 M Ω - μ F min.,
whichever is less

Dielectric Strength

120% rated voltage, 5 seconds

Life Test

100% rated and +125°C

N1500 General Specifications

Capacitance Range

100 pF to 0.47 μ F
(+25°C, 1.0 $\pm$ 0.2 Vrms (open circuit
voltage) at 1kHz)

Capacitance Tolerances

$\pm$ 5%; $\pm$ 10%; 20%

Operating Temperature Range

-55°C to +125°C

Temperature Characteristic

-1500 $\pm$ 250 ppm/°C

Voltage Ratings

600 VDC thru 5000 VDC (+125°C)

Dissipation Factor

0.15% max.
(+25°C, 1.0 $\pm$ 0.2 Vrms (open circuit
voltage) at 1kHz)

Insulation Resistance (+25°C, at 500V)

100K M Ω min., or 1000 M Ω - μ F min.,
whichever is less

Insulation Resistance (+125°C, at 500V)

10K M Ω min., or 100 M Ω - μ F min.,
whichever is less

Dielectric Strength

120% rated voltage, 5 seconds

Life Test

100% rated and +125°C

X7R Dielectric General Specifications

Capacitance Range

100 pF to 2.2 μ F
(+25°C, 1.0 $\pm$ 0.2 Vrms at 1kHz)

Capacitance Tolerances

$\pm$ 10%; $\pm$ 20%; +80%, -20%

Operating Temperature Range

-55°C to +125°C

Temperature Characteristic

$\pm$ 15% (0 VDC)

Voltage Ratings

600 VDC thru 5000 VDC (+125°C)

Dissipation Factor

2.5% max.
(+25°C, 1.0 $\pm$ 0.2 Vrms at 1kHz)

Insulation Resistance (+25°C, at 500V)

100K M Ω min., or 1000 M Ω - μ F min.,
whichever is less

Insulation Resistance (+125°C, at 500V)

10K M Ω min., or 100 M Ω - μ F min.,
whichever is less

Dielectric Strength

120% rated voltage, 5 seconds

Life Test

100% rated and +125°C




Performance of SMPS capacitors can be simulated by downloading SpiCalci software program -

<http://www.avx.com/SpiApps/default.asp#spicalci>


Custom values, ratings and configurations are also available.



High Voltage MLC Radials (SV Style)



SV01 thru SV17



SV52 thru SV59 and SV63 thru SV67

Not RoHS Compliant



For RoHS compliant products,
please select correct termination style.

HIGH VOLTAGE RADIAL LEAD HOW TO ORDER

AVX Styles: SV01 THRU SV67

SV01	A	A	102	K	A	A	*
AVX Style	Voltage	Temperature Coefficient	Capacitance Code	Capacitance Tolerance	Test Level	Leads	Packaging
	600V/630V = C 1000V = A 1500V = S 2000V = G 2500V = W 3000V = H 4000V = J 5000V = K	C0G = A X7R = C N1500 = 4	(2 significant digits + no. of zeros) Examples: 10 pF = 100 100 pF = 101 1,000 pF = 102 22,000 pF = 223 220,000 pF = 224 1 μF = 105	C0G: J = ±5% K = ±10% M = ±20% X7R: K = ±10% M = ±20% Z = +80 -20%	A = Standard B = Hi-Rel*	A = Tin/Lead R = RoHS Compliant	(See Note 1)
Note 1: No suffix signifies bulk packaging which is AVX standard packaging. Use suffix "TR1" if tape and reel is required. Parts are reel packaged per EIA-468.							

Note: Capacitors with X7R dielectrics are not intended for applications across AC supply mains or AC line filtering with polarity reversal. Contact plant for recommendations.

*Hi-Rel screening consists of 100% Group A, Subgroup 1 per MIL-PRF-49467. (Except partial discharge testing is not performed and DWV is at 120% rated voltage).

DIMENSIONS

millimeters (inches)

AVX Style	Length (L) max	Height (H) max	Thickness (T) max	Lead Spacing ±.762 (.030) (S)	LD (Nom)
SV01	6.35 (0.250)	5.59 (0.220)	5.08 (0.200)	4.32 (0.170)	0.64 (0.025)
SV02/SV52	8.13 (0.320)	7.11 (0.280)	5.08 (0.200)	5.59 (0.220)	0.64 (0.025)
SV03/SV53	9.40 (0.370)	7.62 (0.300)	5.08 (0.200)	6.99 (0.275)	0.64 (0.025)
SV04/SV54	11.4 (0.450)	5.59 (0.220)	5.08 (0.200)	7.62 (0.300)	0.64 (0.025)
SV05/SV55	11.9 (0.470)	10.2 (0.400)	5.08 (0.200)	9.52 (0.375)	0.64 (0.025)
SV06/SV56	14.0 (0.550)	7.11 (0.280)	5.08 (0.200)	10.16 (0.400)	0.64 (0.025)
SV07/SV57	14.5 (0.570)	12.7 (0.500)	5.08 (0.200)	12.1 (0.475)	0.64 (0.025)
SV08/SV58	17.0 (0.670)	15.2 (0.600)	5.08 (0.200)	14.6 (0.575)	0.64 (0.025)
SV09/SV59	19.6 (0.770)	18.3 (0.720)	5.08 (0.200)	17.1 (0.675)	0.64 (0.025)
SV10	26.7 (1.050)	12.7 (0.500)	5.08 (0.200)	22.9 (0.900)	0.64 (0.025)
SV11	31.8 (1.250)	15.2 (0.600)	5.08 (0.200)	27.9 (1.100)	0.64 (0.025)
SV12	36.8 (1.450)	18.3 (0.720)	5.08 (0.200)	33.0 (1.300)	0.64 (0.025)
SV13/SV63	7.62 (0.300)	9.14 (0.360)	5.08 (0.200)	5.08 (0.200)	0.51 (0.020)
SV14/SV64	10.2 (0.400)	11.7 (0.460)	5.08 (0.200)	5.08 (0.200)	0.51 (0.020)
SV15/SV65	12.7 (0.500)	14.2 (0.560)	5.08 (0.200)	10.2 (0.400)	0.64 (0.025)
SV16/SV66	22.1 (0.870)	16.8 (0.660)	5.08 (0.200)	20.1 (0.790)	0.81 (0.032)
SV17/SV67	23.6 (0.930)	19.8 (0.780)	6.35 (0.250)	20.3 (0.800)	0.81 (0.032)

TAPE & REEL QUANTITY	
Part	Pieces
SV01	1000
SV02/SV52	1000
SV03/SV53	1000
SV04/SV54	1000
SV05/SV55	1000
SV06/SV56	500
SV07/SV57	500
SV08/SV58	500
SV09/SV59	500
SV10	N/A
SV11	N/A
SV12	N/A
SV13/SV63	1000
SV14/SV64	1000
SV15/SV65	500
SV16/SV66	500
SV17/SV67	400

RoHS	
Part	Available
SV01	Yes
SV02/SV52	Yes
SV03/SV53	Yes
SV04/SV54	Yes
SV05/SV55	Yes
SV06/SV56	Yes
SV07/SV57	Yes
SV08/SV58	Yes
SV09/SV59	Yes
SV10	Yes
SV11	Yes
SV12	Yes
SV13/SV63	Yes
SV14/SV64	Yes
SV15/SV65	Yes
SV16/SV66	Yes
SV17/SV67	Yes

High Voltage MLC Radials (SV Style)



CAPACITANCE VALUE

C0G								
Style	600/630V min./max.	1000V min./max.	1500V min./max.	2000V min./max.	2500V min./max.	3000V min./max.	4000V min./max.	5000V min./max.
SV01	100 pF / 1500 pF	100 pF / 1000 pF	10 pF / 330 pF	10 pF / 220 pF	10 pF / 120 pF	10 pF / 82 pF	—	—
SV02/SV52	100 pF / 6800 pF	100 pF / 4700 pF	100 pF / 1500 pF	10 pF / 1000 pF	10 pF / 680 pF	10 pF / 560 pF	10 pF / 150 pF	10 pF / 100 pF
SV03/SV53	100 pF / 0.012 μ F	100 pF / 8200 pF	100 pF / 2700 pF	100 pF / 1800 pF	10 pF / 1000 pF	10 pF / 680 pF	10 pF / 390 pF	10 pF / 220 pF
SV04/SV54	100 pF / 3900 pF	100 pF / 2700 pF	10 pF / 820 pF	10 pF / 560 pF	10 pF / 270 pF	10 pF / 180 pF	10 pF / 100 pF	10 pF / 68 pF
SV05/SV55	1000 pF / 0.027 μ F	1000 pF / 0.018 μ F	100 pF / 6800 pF	100 pF / 4700 pF	100 pF / 2700 pF	100 pF / 1500 pF	10 pF / 1000 pF	10 pF / 560 pF
SV06/SV56	100 pF / 0.012 μ F	100 pF / 0.010 μ F	100 pF / 3300 pF	100 pF / 2200 pF	10 pF / 1200 pF	10 pF / 820 pF	10 pF / 470 pF	10 pF / 390 pF
SV07/SV57	1000 pF / 0.056 μ F	1000 pF / 0.033 μ F	1000 pF / 0.015 μ F	100 pF / 0.010 μ F	100 pF / 5600 pF	100 pF / 3900 pF	100 pF / 2200 pF	10 pF / 1200 pF
SV08/SV58	1000 pF / 0.082 μ F	1000 pF / 0.047 μ F	1000 pF / 0.022 μ F	1000 pF / 0.015 μ F	100 pF / 0.010 μ F	100 pF / 6800 pF	100 pF / 3300 pF	100 pF / 2200 pF
SV09/SV59	1000 pF / 0.150 μ F	1000 pF / 0.082 μ F	1000 pF / 0.039 μ F	1000 pF / 0.022 μ F	1000 pF / 0.015 μ F	100 pF / 8200 pF	100 pF / 4700 pF	100 pF / 3300 pF
SV10	1000 pF / 0.100 μ F	1000 pF / 0.056 μ F	1000 pF / 0.022 μ F	1000 pF / 0.012 μ F	100 pF / 8200 pF	100 pF / 5600 pF	100 pF / 3300 pF	100 pF / 2200 pF
SV11	1000 pF / 0.150 μ F	1000 pF / 0.082 μ F	1000 pF / 0.039 μ F	1000 pF / 0.022 μ F	1000 pF / 0.015 μ F	100 pF / 8200 pF	100 pF / 4700 pF	100 pF / 3300 pF
SV12	0.01 μ F / 0.220 μ F	0.01 μ F / 0.15 μ F	1000 pF / 0.056 μ F	1000 pF / 0.033 μ F	1000 pF / 0.022 μ F	1000 pF / 0.015 μ F	100 pF / 8200 pF	100 pF / 5600 pF
SV13/SV63	100 pF / 0.018 μ F	100 pF / 0.012 μ F	100 pF / 4700 pF	100 pF / 2700 pF	100 pF / 1800 pF	100 pF / 1000 pF	10 pF / 470 pF	10 pF / 390 pF
SV14/SV64	1000 pF / 0.039 μ F	1000 pF / 0.022 μ F	100 pF / 8200 pF	100 pF / 5600 pF	100 pF / 3300 pF	100 pF / 1800 pF	10 pF / 820 pF	10 pF / 680 pF
SV15/SV65	1000 pF / 0.056 μ F	1000 pF / 0.033 μ F	1000 pF / 0.015 μ F	100 pF / 0.01 μ F	100 pF / 5600 pF	100 pF / 2700 pF	100 pF / 1800 pF	100 pF / 1200 pF
SV16/SV66	1000 pF / 0.120 μ F	1000 pF / 0.082 μ F	1000 pF / 0.039 μ F	1000 pF / 0.027 μ F	1000 pF / 0.015 μ F	100 pF / 8200 pF	100 pF / 4700 pF	100 pF / 3300 pF
SV17/SV67	1000 pF / 0.150 μ F	1000 pF / 0.10 μ F	1000 pF / 0.056 μ F	1000 pF / 0.039 μ F	1000 pF / 0.022 μ F	1000 pF / 0.012 μ F	100 pF / 6800 pF	100 pF / 4700 pF
N1500								
SV01	1000 pF / 2700 pF	1000 pF / 1800 pF	100 pF / 680 pF	100 pF / 470 pF	100 pF / 220 pF	100 pF / 150 pF	—	—
SV02/SV52	1000 pF / 0.012 μ F	1000 pF / 8200 pF	1000 pF / 2700 pF	1000 pF / 1800 pF	100 pF / 1000 pF	100 pF / 680 pF	100 pF / 270 pF	100 pF / 150 pF
SV03/SV53	0.010 pF / 0.027 μ F	0.010 pF / 0.018 μ F	1000 pF / 5600 pF	1000 pF / 3900 pF	1000 pF / 2200 pF	1000 pF / 1500 pF	100 pF / 680 pF	100 pF / 470 pF
SV04/SV54	1000 pF / 8200 pF	1000 pF / 5600 pF	1000 pF / 1800 pF	100 pF / 1200 pF	100 pF / 560 pF	100 pF / 330 pF	100 pF / 220 pF	100 pF / 120 pF
SV05/SV55	0.010 μ F / 0.068 μ F	0.010 μ F / 0.047 μ F	0.010 μ F / 0.015 μ F	1000 pF / 0.010 μ F	1000 pF / 5600 pF	1000 pF / 3300 pF	1000 pF / 2200 pF	1000 pF / 1200 pF
SV06/SV56	0.010 μ F / 0.027 μ F	0.010 μ F / 0.018 μ F	1000 pF / 5600 pF	1000 pF / 3900 pF	1000 pF / 2200 pF	1000 pF / 1500 pF	100 pF / 680 pF	100 pF / 470 pF
SV07/SV57	0.010 μ F / 0.12 μ F	0.010 μ F / 0.10 μ F	0.010 μ F / 0.027 μ F	0.010 μ F / 0.018 μ F	1000 pF / 0.012 μ F	1000 pF / 5600 pF	1000 pF / 3900 pF	1000 pF / 2200 pF
SV08/SV58	0.010 μ F / 0.15 μ F	0.010 μ F / 0.12 μ F	0.010 μ F / 0.047 μ F	0.010 μ F / 0.033 μ F	0.010 μ F / 0.018 μ F	1000 pF / 0.010 μ F	1000 pF / 6800 pF	1000 pF / 3900 pF
SV09/SV59	0.10 μ F / 0.220 μ F	0.10 μ F / 0.18 μ F	0.010 μ F / 0.082 μ F	0.010 μ F / 0.047 μ F	0.010 μ F / 0.033 μ F	0.010 μ F / 0.015 μ F	1000 pF / 8200 pF	1000 pF / 6800 pF
SV10	0.10 μ F / 0.18 μ F	0.10 μ F / 0.15 μ F	0.010 μ F / 0.047 μ F	0.010 μ F / 0.027 μ F	0.010 μ F / 0.018 μ F	1000 pF / 0.010 μ F	1000 pF / 5600 pF	1000 pF / 3900 pF
SV11	0.10 μ F / 0.33 μ F	0.10 μ F / 0.22 μ F	0.010 μ F / 0.082 μ F	0.010 μ F / 0.039 μ F	0.010 μ F / 0.027 μ F	0.010 μ F / 0.018 μ F	1000 pF / 0.010 μ F	1000 pF / 6800 pF
SV12	0.10 μ F / 0.47 μ F	0.10 μ F / 0.33 μ F	0.10 μ F / 0.12 μ F	0.010 μ F / 0.068 μ F	0.010 pF / 0.047 μ F	0.010 μ F / 0.027 μ F	0.010 μ F / 0.015 μ F	1000 pF / 0.010 μ F
SV13/SV63	0.010 μ F / 0.039 μ F	0.010 μ F / 0.027 μ F	1000 pF / 8200 pF	1000 pF / 5600 pF	1000 pF / 3300 pF	1000 pF / 1800 pF	100 pF / 820 pF	100 pF / 680 pF
SV14/SV64	0.010 μ F / 0.082 μ F	0.010 μ F / 0.056 μ F	0.010 pF / 0.018 μ F	1000 pF / 0.012 μ F	1000 pF / 6800 pF	1000 pF / 3900 pF	1000 pF / 1800 pF	1000 pF / 1500 pF
SV15/SV65	0.010 μ F / 0.10 μ F	0.010 μ F / 0.082 μ F	0.010 μ F / 0.027 μ F	0.010 pF / 0.018 μ F	1000 pF / 0.012 μ F	1000 pF / 5600 pF	1000 pF / 3300 pF	1000 pF / 2700 pF
SV16/SV66	0.10 μ F / 0.22 μ F	0.10 μ F / 0.18 μ F	0.010 μ F / 0.082 μ F	0.010 μ F / 0.039 μ F	0.010 μ F / 0.027 μ F	0.010 μ F / 0.015 μ F	1000 pF / 8200 pF	1000 pF / 6800 pF
SV17/SV67	0.10 μ F / 0.33 μ F	0.10 μ F / 0.22 μ F	0.010 μ F / 0.10 μ F	0.010 μ F / 0.056 μ F	0.010 μ F / 0.033 μ F	0.010 μ F / 0.022 μ F	1000 pF / 0.012 μ F	1000 pF / 0.010 μ F
X7R								
SV01	1000 pF / 0.018 μ F	1000 pF / 0.012 μ F	100 pF / 5600 pF	100 pF / 3900 pF	—	—	—	—
SV02/SV52	1000 pF / 0.082 μ F	1000 pF / 0.047 μ F	1000 pF / 0.015 μ F	100 pF / 6800 pF	100 pF / 3900 pF	100 pF / 2700 pF	—	—
SV03/SV53	1000 pF / 0.180 μ F	1000 pF / 0.082 μ F	1000 pF / 0.018 μ F	1000 pF / 0.01 μ F	100 pF / 6800 pF	100 pF / 4700 pF	100 pF / 1800 pF	—
SV04/SV54	1000 pF / 0.056 μ F	1000 pF / 0.033 μ F	100 pF / 6800 pF	100 pF / 3900 pF	100 pF / 2200 pF	100 pF / 1800 pF	100 pF / 820 pF	—
SV05/SV55	0.01 μ F / 0.470 μ F	0.01 μ F / 0.22 μ F	1000 pF / 0.056 μ F	1000 pF / 0.027 μ F	1000 pF / 0.018 μ F	1000 pF / 0.012 μ F	100 pF / 4700 pF	—
SV06/SV56	0.01 μ F / 0.180 μ F	0.01 μ F / 0.10 μ F	1000 pF / 0.033 μ F	1000 pF / 0.012 μ F	100 pF / 8200 pF	100 pF / 6800 pF	100 pF / 2700 pF	100 pF / 1200 pF
SV07/SV57	0.01 μ F / 0.820 μ F	0.01 μ F / 0.39 μ F	0.01 μ F / 0.10 μ F	1000 pF / 0.047 μ F	1000 pF / 0.033 μ F	1000 pF / 0.027 μ F	1000 pF / 0.01 μ F	100 pF / 6800 pF
SV08/SV58	0.01 μ F / 1.20 μ F	0.01 μ F / 0.68 μ F	0.01 μ F / 0.18 μ F	1000 pF / 0.082 μ F	1000 pF / 0.068 μ F	1000 pF / 0.047 μ F	1000 pF / 0.018 μ F	1000 pF / 0.012 μ F
SV09/SV59	0.10 μ F / 1.80 μ F	0.01 μ F / 1.00 μ F	0.01 μ F / 0.27 μ F	0.01 μ F / 0.12 μ F	0.01 μ F / 0.10 μ F	1000 pF / 0.068 μ F	1000 pF / 0.027 μ F	1000 pF / 0.018 μ F
SV10	0.01 μ F / 1.50 μ F	0.01 μ F / 0.82 μ F	0.01 μ F / 0.22 μ F	0.01 μ F / 0.10 μ F	1000 pF / 0.082 μ F	1000 pF / 0.056 μ F	1000 pF / 0.022 μ F	1000 pF / 0.022 μ F
SV11	0.10 μ F / 2.20 μ F	0.10 μ F / 1.2 μ F	0.01 μ F / 0.39 μ F	0.01 μ F / 0.18 μ F	0.01 μ F / 0.15 μ F	0.01 μ F / 0.10 μ F	1000 pF / 0.039 μ F	1000 pF / 0.027 μ F
SV12	0.10 μ F / 3.90 μ F	0.10 μ F / 2.20 μ F	0.01 μ F / 0.56 μ F	0.01 μ F / 0.27 μ F	0.01 μ F / 0.22 μ F	0.01 μ F / 0.15 μ F	1000 pF / 0.056 μ F	1000 pF / 0.033 μ F
SV13/SV63	0.01 μ F / 0.270 μ F	0.01 μ F / 0.10 μ F	1000 pF / 0.033 μ F	1000 pF / 0.012 μ F	1000 pF / 0.01 μ F	100 pF / 6800 pF	100 pF / 2700 pF	—
SV14/SV64	0.01 μ F / 0.470 μ F	0.01 μ F / 0.18 μ F	1000 pF / 0.068 μ F	1000 pF / 0.022 μ F	1000 pF / 0.018 μ F	1000 pF / 0.015 μ F	100 pF / 5600 pF	—
SV15/SV65	0.01 μ F / 0.680 μ F	0.01 μ F / 0.33 μ F	0.01 μ F / 0.10 μ F	1000 pF / 0.033 μ F	1000 pF / 0.027 μ F	1000 pF / 0.022 μ F	1000 pF / 8200 pF	100 pF / 4700 pF
SV16/SV66	0.01 μ F / 1.80 μ F	0.01 μ F / 1.0 μ F	0.01 μ F / 0.27 μ F	0.01 μ F / 0.12 μ F	0.01 μ F / 0.10 μ F	1000 pF / 0.068 μ F	1000 pF / 0.027 μ F	1000 pF / 0.018 μ F
SV17/SV67	0.01 μ F / 2.20 μ F	0.01 μ F / 1.2 μ F	0.01 μ F / 0.39 μ F	0.01 μ F / 0.15 μ F	0.01 μ F / 0.12 μ F	1000 pF / 0.082 μ F	1000 pF / 0.039 μ F	1000 pF / 0.027 μ F

Note: Contact factory for other voltage ratings or values.



AVX IS QUALIFIED TO THE FOLLOWING DSCC DRAWINGS

Specification #	Description	Capacitance Range
87046	C0G-1000 VDC	10 pF - 0.025 μ F
87043	X7R-1000 VDC	100 pF - 0.47 μ F
87040	X7R-2000 VDC	100 pF - 0.22 μ F
87114	C0G-3000 VDC	10 pF - 8200 pF
87047	X7R-3000 VDC	100 pF - 0.1 μ F
87076	C0G-4000 VDC	10 pF - 6800 pF
89044	X7R-4000 VDC	100 pF - 0.056 μ F
87077	C0G-5000 VDC	10 pF - 5600 pF
87070	X7R-5000 VDC	100 pF - 0.033 μ F

Group A inspection

Inspection	Requirement paragraph of MIL-PRF-49467	Test method paragraph of MIL-PRF-49467	Sampling procedure
Subgroup 1 Thermal Shock Voltage Conditioning	3.6 3.6	4.8.2.1 4.8.2.2	100% Inspection
Subgroup 2 Visual and mechanical examination: Material Physical dimensions Interface requirements (other than physical dimensions) Marking Workmanship	3.4 and 3.4.1 3.1 3.5 3.25 3.27	4.8.4	13 samples 0 failures
Subgroup 4 Solderability	3.13	4.8.9	13 samples 0 failures

Group B inspection*

Inspection	Requirement paragraph of MIL-PRF-49467	Test method paragraph of MIL-PRF-4946	Number of sample units to be inspected	Number of defectives permitted	
Subgroup 1 Terminal strength Resistance to soldering heat Moisture resistance	3.18 3.11 3.19	4.8.14 4.8.7 4.8.15	12	1	1
Subgroup 2 Voltage-temperature limits** Low temperature storage Marking legibility	3.14 3.23 3.25.1	4.8.10 4.8.19 4.8.1.1	6	1	
Subgroup 3 Resistance to solvents	3.21	4.8.17	4	1	
Subgroup 3 Life (at elevated ambient temperature)	3.21	4.8.17	10	1	

*Customers may accept at their discretion, a certificate of compliance with group B requirements in lieu of performing group B tests.

**For Steps E, F & G in Table VII of MIL-PRF-49467, 500 Vdc shall be applied.