





Push buttons diameter 12 and actuators





Features	Actuator color	Valve color	Push button round	Push button double round
Version	NC	black	81 735 511	—
		red	81 735 512	—
		black/red	—	81 733 511
	NO	black	81 735 011	—
		red	—	—
		black/red	—	—

Symbol

NC



NO




Characteristics


Operating pressure	bar	2 → 8	2 → 8
Orifice diameter	mm	2.7	2.7
Flow at 6 bars	l/min.	200	200
Valves	NC : black NO : grey	• •	• •
Operating forces (depending on actuator)	N	8 → 18	8 → 18
Effective travel	mm	1	1
Fluid: dry or lubricated air		•	•
Push-in connectors for semi-rigid tubing (NFE 49100)	mm	Ø 4	Ø 4
Operating temperature	°C	-5 +50	-5 +50
Mechanical life	operations	1.5 x 10 ⁶	1.5 x 10 ⁶
Weight	g	35	40

Dimensions


81 735




81 733





Threaded barrel



2 threaded barrels





3-position lever
manual return

81 716 511
81 716 512

3-position lever
spring return

81 715 511
81 715 512

Horizontal outputs

81 280 510

Vertical outputs



81 281 510

—
—
—
—

—
—
—
—

—
81 280 010
—
—

—
81 281 010
—
—



2 → 8
2.7
200

•
•
8 → 18
1

•

Ø 4

-5 +50
1.5 x 10⁶
65

2 → 8
2.7
200

•
•
8 → 18
1

•

Ø 4

-5 +50
1.5 x 10⁶
65

2 → 8
2.7
200

—
—
—
1

Ø 4

-5 +50
1.5 x 10⁶
14


2 → 8
2.7
200

—
—
—
1


Ø 4

-5 +50
1.5 x 10⁶
14


81 715 - 81 716




Square lever



81 280 010 - 81 280 510



81 281 010 - 81 281 510



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Crouzet:

[81715512](#) [89543501](#) [89543101](#) [89543701](#) [89543201](#) [89543305](#) [89543205](#) [89538201](#) [89543005](#)