




3M™ TEXTTOOL™ OPEN-TOP SOCKETS FOR QFN APPLICATIONS



NOTES:

1. MATERIALS:

SPRINGS	SS	PLATING : Au
CONTACTS	Be Cu	COLOR : BLACK
IC GUIDES	PES	COLOR : BLACK
PRESSURE PAD	PES	COLOR : BLACK
COVER	PPS or equiv.	COLOR : BLACK
BASE	PES	COLOR : BLACK



2. SEE THE REGULATORY INFORMATION APPENDIX (RIA) IN THE "RoHS COMPLIANCE" SECTION WWW.3MCONNECTOR.COM FOR COMPLIANCE INFORMATION (RIA E1 & C1 APPLY).


3. FOR PRODUCT SPECIFICATIONS AND WARRANTY INFORMATION SEE:

WWW.3MCONNECTOR.COM PN 240-5205-00

DESIGN REFERENCE		NEXT ASSEMBLY		A 37213 INITIAL RELEASE		ARM	
DISTRIBUTION CODES		SCALE 5/1		TOLERANCES EXCEPT AS NOTED		3M 3M Center St. Paul, MN 55144	
DIVISION		DIVISION CODE		INCHES .0 ± .1 .00 ± .02 .000 ± .005 .0000 ± .0002		MILLIMETERS 0 ± .0 .00 ± .000 ± .0000	
THIRD ANGLE PROJECTION		INTERPRET PER ASME Y14.5 - 1994		MAX SURFACE ROUGHNESS 125 ✓		CAGE NUMBER C	
DO NOT SCALE DRAWING		SCALE 5/1		TOLERANCES EXCEPT AS NOTED		TITLE QFN TEST SOCKET, 0.5mm 40 pos, EVEN ROW, 6X6 PKG NO TP	
MAX SURFACE ROUGHNESS 125 ✓		SCALE 5/1		TOLERANCES EXCEPT AS NOTED		DRAWING NO. 78-5100-2469-4	
INTERPRET PER ASME Y14.5 - 1994		SCALE 5/1		TOLERANCES EXCEPT AS NOTED		REV. A	
MAX SURFACE ROUGHNESS 125 ✓		SCALE 5/1		TOLERANCES EXCEPT AS NOTED		MODEL TEXTTOOL - QFN	
DO NOT SCALE DRAWING		SCALE 5/1		TOLERANCES EXCEPT AS NOTED		DET. LISTS	
INTERPRET PER ASME Y14.5 - 1994		SCALE 5/1		TOLERANCES EXCEPT AS NOTED		SHT 1 OF 2	
MAX SURFACE ROUGHNESS 125 ✓		SCALE 5/1		TOLERANCES EXCEPT AS NOTED		ANGLES ± 1°	

3M™ TEXTTOOL™ OPEN-TOP SOCKETS FOR QFN APPLICATIONS



DESIGN REFERENCE				NEXT ASSEMBLY				REV	ECO	ISSUE DATE AND DESCRIPTION				DRFT	CHKD
DISTRIBUTION CODES								DRFT		DATE		MFG		DATE	
								CHKD		DATE		APPVL		DATE	
DIVISION				DIVISION CODE				3M3M Center St. Paul, MN 55144 © 3M COPYRIGHT 2012 This document is the copyrighted property of the 3M Company and may not be reproduced without 3M written permission or used for other than 3M authorized purposes.							
DO NOT SCALE DRAWING		SCALE 5 1		TOLERANCES EXCEPT AS NOTED											
				INCHES				TITLE QFN TEST SOCKET, 0.5mm 40 pos, EVEN ROW, 6X6 PKG NO TP							
				.0 ± .1 .00 ± .02 .000 ± .005 .0000 ± .0002											
THIRD ANGLE PROJECTION INTERPRET PER ASME Y14.5 - 1994				MILLIMETERS				CAGE NUMBER SIZE DRAWING NO. REV.							
MAX SURFACE ROUGHNESS 125 ✓ ☐ ALL SURFACES ☒ MARKED ONLY				0 ± .1 .0 ± .005 .00 ± .0002											
				ANGLES ± 1°				TEXTTOOL - QFN				DET. LISTS ☐ YES ☒ NO		SHT 2 OF 2	