



### Main

|                           |  |
|---------------------------|--|
| Range                     | Spacial  |
| Product name              | Spacial SBM  |
| Device application        | Multi-purpose                                      |
| Product or component type | Industrial box                                     |
| Device short name         | SBM  |
| Enclosure type            | Flat face box                                      |
| Enclosure nominal height  | 200 mm   |
| Enclosure nominal width   | 800 mm   |
| Enclosure nominal depth   | 120 mm   |
| Enclosure mounting        | Wall mounted                                       |
| Device composition        | 6 x cover screw<br>1 x body<br>1 x cover           |
| Body type                 | Single piece body folded and welded                |
| Type of front cover       | Plain door   |
| Cover fixing              | Half turn metal screw                              |
| Lock type                 | Outside sealed area: PZ2 screwdriver captive screw |
| Removable parts           | Cover, by captive screws                           |

### Complementary

|                        |                             |
|------------------------|-----------------------------|
| Material               | Sheet steel                 |
| Surface finish         | Polyester powder            |
| Colour                 | Grey ( RAL 7035 )           |
| Standards              | IEC 62208                   |
| Product certifications | DNV<br>GL<br>LR<br>BV<br>UL |

|                                       |                              |
|---------------------------------------|------------------------------|
| IP degree of protection               | IP66 IEC 60529               |
| IK degree of protection               | IK10 conforming to IEC 62262 |
| Ambient air temperature for storage   | -35...60 °C                  |
| Ambient air temperature for operation | -35...80 °C                  |

### Offer Sustainability

|                                  |   |
|----------------------------------|---|
| Sustainable offer status         | Green Premium product   |
| RoHS (date code: YYWW)           | Compliant - since 1241 - Schneider Electric declaration of conformity<br><a href="#">Schneider Electric declaration of conformity</a> |
| REACH                            | Reference not containing SVHC above the threshold<br><a href="#">Reference not containing SVHC above the threshold</a>                |
| Product environmental profile    | Available   |
| Product end of life instructions | Need no specific recycling operations   |

### Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|