

7

6

5

4


3

2

1

REVISIONS

EC NO	DATE	REV	DESCRIPTION	CHANGER
CY13-5876	13.01.09	B	CHG. TITLE	JORRY
CY13-5950	13.01.25	C	CANCEL TINNED	JORRY



NOTES

1. THIS PRODUCT MUST MEET EU 2002/95 EC ROHS COMPLIANCE.

此产品需符合EU 2002/95 EC ROHS 环保要求

2. ELECTRICAL PERFORMANCE REFER TO ES-000.

电气特性参考ES-000.

3. 28AWG WIRE SPEC.(线的规格)

1) WIRE OD:0.7+/-0.05MM,

2) WIRE INSULATION: FEP

3) CONDUCTOR:7/0.127 TINNED COPPER

4)UL STYLE:UL1371

5)TEMPERATURE RATING:105℃

6) RATED VOLTAGE:300V

4. 18AWG WIRE SPEC.(线的规格)

1) WIRE OD:2.05+/-0.05MM,

2) WIRE INSULATION: PVC

3) CONDUCTOR:34/0.178 TINNED COPPER

4)UL STYLE:UL1569

5)TEMPERATURE RATING:105℃

6) RATED VOLTAGE:300V

5. STICK UL LABEL ON THE OUTSIDE CARTON.

外箱上贴UL 标签

G	HST 2MM BLACK	A/R	
F	18AWG/34STD,PLTD,PVC,RD,OD=2.05MM,UL1569	A/R	
E	18AWG/34STD,PLTD,PVC,BK,OD=2.05MM,UL1569	A/R	
D	28AWG,FEP,RED,OD:0.7MM,UL1371,VW-1	A/R	
C	28AWG,FEP,BLACK,OD:0.7MM,UL1371,VW-1	A/R	
B	TERMINAL 28-30AWG		2
A	4CKT HSG,WHITE		1
ITEM	DESCRIPTION	L(MM)	Q'TY

WIRING CHART	
P1	COLOR
1	RED
2	
3	
4	BLACK

EC NO: CPG2013-2410 DRWN: CXIA003 CHKD: JDUAN APPR: FNIE	DESCRIPTION REV	QUALITY SYMBOLS F _A =0 F _C =0 F _P =0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY CXIA003	DATE 2012/12/25	TITLE 2PINS WIRING PICO EZMATE 18" 18/28AWG B	molex			
			4 PLACES	± ---	± ---	CHECKED BY JDUAN	DATE 2012/12/25					
			3 PLACES	± ---	± ---	APPROVED BY FNIE	DATE 2012/12/26					
			2 PLACES	± ---	± ---	MATERIAL NO. 688014229			DOCUMENT NO. SD-68801-094			SHEET NO. 1 OF 1
			1 PLACE	± ---	± ---							
			0 PLACE	± ---	± ---	SIZE A 4			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOTBE USED WITHOUT WRITTEN PERMISSION			
			ANGULAR ±---°									
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS									

6

5

4

3

2

1