

APPLICATOR PARTS LIST

TYPE

HINGE-BAR MARK III (LH)

AMP INCORPORATED
HARRISBURG, PENNA.

THIS IS A CONTROLLED DOCUMENT.

NO. DESCRIPTION REQ. PART NO.				NO. DESCRIPTION REQ. PART NO.				CRIMPING DATA				TERMINALS
1	■ WIRE CRIMPER	1	460028-1	42	FRONT STAB. BAR	1	811006-1	TO APPLY TERMINAL SPEC 114-2078				62056
2	■ INS. CRIMPER			43				WIRE SIZE				
3	■ ANVIL	1	843101-1	44	HINGE BLOCK & STAB.	1	811444-1	CRIMP HEIGHT				
4	ANVIL INSERT	1	460027-1	45	HINGE PIN	1	811007-1	12	.072			
5	■ SHEAR BLADE	1	460026-1	46	GUARD, FRONT STAB.	1	811040-1	14	.062			
6	■ REAR SHEAR PLATE	1	460025-1	47	HINGE BAR ASS'Y	1	565098-1	16	.056			
7	SHEAR BLADE SPRING	1	810410-1	48	HINGE BAR SPRING	2	3-23846-5	18	.052			
8	■ FRONT SHEAR PLATE	1	388632-5	49	STRIP GUIDE STOP	2	810417					
9	REAR ANVIL SPACER PLT.			50	STRIP HOLD DOWN			CRIMP	SIZE	TYPE	FEED	
10	FRONT ANVIL SPACER PLT.			51	SPACER COMP. SPRING	2	811070-1	WIRE	.160	TL	.760	
11	TOOL SPACER			52	CAM FOLLOWER HOLDER	1	810409-1	INSUL.	++	++		
12	CRIMP SPACER			53	CAM FOLLOWER	1	24746-1	SLEEVED	++	++		
13	FRONT STRIP GUIDE	1	811566-2	54	SPRING, BRACKET	1	810418	INSULATION RANGE		WIRE RANGE		
14	REAR STRIP GUIDE	1	460023-3	55	CAM FOLLOWER SPRING	1	810408	++		18-12		
				56	HOOK HOLDER	1	811442-1	EXPLODED VIEW				
15	RAM	1	811450-1	57	SHEAR PICK-UP HOOK	1	811443-1	A-6004-5 A-6004-6				
16	RAM RET. PL.	1	465004-2	58	HOLD DOWN-HINGE BAR	1	811009-1	REMARKS:				
17	ADJ. PLATE	1	811010-1	59	DEPRESSOR SCREW	1	810642-1	LEFT HAND				
18	PROTECTIVE PLUG	1	23141-1	60	WASHER	2	376482	⚠ ITEMS 68 & 72 MOUNT TO REEL SUPPORT SHAFT TO SUPPORT TERMINAL REEL. ⚠ FOR TERMINAL 62056 PRIOR TO REV W USE ANVIL P/N 692901-1 ■ RECOMMENDED SPARE PARTS				
19	APPLICATOR MOUNT ASSY.			61	FEED FINGER SPRING	1	810421-1					
20	BASE PLATE	1	465408-1	62	DOWEL PIN	2	1-21030-5					
21	BASE BLOCK			63	MICRO-SWITCH	1	23496-1					
22	STRIP GUIDE PLATE			64	MICRO-SWITCH COVER	1	22689-2					
23	ANVIL HOLDER	1	811445-1	65	BRACKET, MICRO-SWITCH	1	811074-1					
24	AUX. ANVIL HOLDER			MISCELLANEOUS								
25	STRIPPER			66	CONNECTOR	1	22787-2					
26	STRIPPER MOUNT			67	HOOK HOLDER SCREW	1	810413					
27	RETAINER PLATE			68	SCR, SOC HD CAP 1/4-20x1.00	2	21001-6					
28	STRIPPER MOUNT BRACKET			69	SPACER (ANVIL HOLDER)	1	811223-1					
29	STRIPPER BUSHING			70	LEAD WIRE	1	465918-1	THIS APPLICATOR IS TO BE USED ON				
30	STOCK DRAG	1	460024-1	71	DOWEL PIN	1	465702-1	AMP-O-LECTRIC 1-471273-3				
31	STOCK DRAG HANDLE			72	WASHER, BEVELED	2	682131-1	AMP-O-MATIC				
32	STOCK DRAG STUD			REV. REVISION RECORD			DATE	BY	ECN			
33	STOCK DRAG SPRING	2	810135	A	REV. PER ECN		11/676	JW	R1491			
34	STOCK DRAG ADJ. SCREW			B	ADD ITEMS 68 & 72		11/13/78	JE	R2752			
35	FEED FINGER HOLDER	1	810131	C	REV PER ECN		1-8-79	KS	R2834			
36	FEED FINGER	1	811440-2	D	REV PER ECN R5199		6-27-93	SG				
37	FEED FINGER TIP	1	811439-1	E	ECN: A-095188		6-23-88	JS				
38	FEED FINGER STUD	1	810414-1	F	ECN A-128588		8-17-88	JS				
39	BASE CASTING	1	811451-1	F1	ECN 0150-1144-04		9-64	MY	TE			
40	GUARD	1	461100-1									
41												

SERIAL NO.		DATE SHIPPED		DESIGNED
				10-20-77
CUSTOMER NAME AND ADDRESS				CHK'D.
				11/11/77
				6-19-77
				APP'D.
				6-19-77
APPLICATOR NUMBER		REV.	SHEET	
		F1	566154-1 1 OF 1	

CASE CODE
00779

CUSTOMER AND ASSEMBLY DRAWING

RESTRICTED TO

FOR HARDWARE SEE 687520-

DIST.

DESIGNED

CHK'D

11/11/78

6-18-79

APP'D

6-19-79

SHEET

1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[566154-1](#)