


REV.	DATE	ECR NO.	DESCRIPTION
NC	03/06/00	—	INITIAL RELEASE
A	06/03/08	100024	UPDATE DRAWING FORMAT, INSULATOR REVISED TO PTFE



				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"	APPROVALS		DATE		Amphenol Connex					
8					DRAWN	GRS	06/03/08							
7					CHECKED			PART DESCRIPTION N MALE TO F FEMALE W/WATERPROOF ADAPTER						
6					ISSUED									
5					SHEET	1 OF 1								
4	GASKET	SILICONE	RED	1					PART NO. 242156					
3	CONTACT PIN	BER. COPPER	GOLD	1										
2	INSULATOR	PTFE	NATURAL	1					DWG. NO. 242156.DWG					
1	BODY	BRASS	NICKEL	1										
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING		CAD FILE C:/242/242156.DWG		REV.	A	SIZE	A	SCALE	NA